

FPQ3-96SW

Model name	FPQ3-96SW
LED color	White
Input voltage	24 VDC
Power consumption(max.)	25 W
Weight(max.)	170 g
Connector	SMR-03V-B
Polarity and signal	1:(+) 2:NC 3:(-)

Unit: mm

