


[All Products](#) /
 [Optics](#) /
 [Optical Mirrors](#) /
 [Flat Mirrors](#) /
 [Laser Mirrors](#)

TECHSPEC® Precision Broadband Laser Mirrors



- Ideal for Tunable Lasers and Reflecting Multiple Laser Sources
- High Reflectivity from 0 - 45° for All Polarization States
- Variety of Coating Options Available

Common Specifications

General

Note:

Optical Power: $\lambda/10$

Physical & Mechanical Properties

Back Surface:

Ground



Optical Properties

Surface Quality: 20-10


Irregularity (P-V) @
632.8nm: $\lambda/20$

Angle of Incidence (°): 0-45


Technical Information



Mirror for UV 300-500nm



Mirror for Near-IR



Products

Wavelength Range (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
300 - 550	12.70	5.00	0-45	#48-015	C\$197.40 Volume Pricing	Contact Us
300 - 550	25.40	8.00	0-45	#48-016	C\$243.60 Volume Pricing	5 In Stock
400 - 700	12.70	5.00	0-45	#45-754	C\$197.40 Volume Pricing	20+ In Stock
400 - 700	25.40	8.00	0-45	#45-596	C\$243.60 Volume Pricing	Contact Us
#75-420 New						
 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!						
400 - 700	50.80	12.50	0-45		C\$491.40 Volume Pricing	9 In Stock
700 - 900	12.70	5.00	0-45	#45-755	C\$197.40 Volume Pricing	20+ In Stock
700 - 900	25.40	8.00	0-45	#45-597	C\$243.60 Volume Pricing	20+ In Stock

[#75-421 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

700 - 900

50.80

12.50

0-45

C\$491.40
[Volume Pricing](#)

8 In Stock

450 - 12000

12.70

5.00

0-45

[#45-757](#)

C\$197.40
[Volume Pricing](#)

20+ In Stock

450 - 12000

25.40

8.00

0-45

[#45-758](#)

C\$243.60
[Volume Pricing](#)

Contact Us

450 - 12000

50.80

12.50

0-45

[#48-017](#)

C\$491.40
[Volume Pricing](#)

16 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com