

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives [See More by Mitutoyo](#)



- Ideal for Bright Field Imaging in UV, Visible, and NIR Spectral Regions
- Excellent Performance at Nd:YAG Laser Lines
- Broad Spectral Ranges

Common Specifications

General

Compatible Tube Lens Focal Length (mm):	Focal Length: 200mm	Manufacturer:	Mitutoyo
--	---------------------	---------------	----------

Optical Properties

Compatible Cover Glass Thickness (mm):	N/A	Immersion Liquid:	N/A
---	-----	-------------------	-----


Threading & Mounting

Mounting Threads:	M26 x 36 TPI
-------------------	--------------

Environmental & Durability Factors

Operating Temperature (°C):	-5 to +45
Operating Humidity:	20 - 80%

Technical Information



Products

Magnification	NA	DWL (nm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
5X	0.14	532, 1064	40.00	378-822- 5	37.5	#46-402	C\$2,828.00	8 In Stock
10X	0.26	532, 1064	20.00	378-823- 15	30.5	#46-403	C\$3,248.00	4 In Stock
20X	0.40	532, 1064	10.00	378-824- 16	20.0	#46-404	C\$5,698.00	5 In Stock
50X	0.42	532, 1064	4.00	378-825- 17	17.0	#46-405	C\$6,510.00	3 In Stock
100X	0.50	532, 1064	2.00	378-826- 15	12.0	#46-406	C\$9,492.00	5 In Stock
50X	0.65	532, 1064	4.00	378-863- 5	10.0	#56-982	C\$15,820.00	Contact Us
20X	0.40	532, 1064	10.00	378-867- 5	25.5	#89-350	C\$7,658.00	1 In Stock
50X	0.42	532, 1064	4.00	378-868- 5	25.5	#89-351	C\$10,094.00	2 In Stock
100X	0.70	532, 1064	2.00	378-864- 15	10.0	#56-983	C\$15,680.00	2 In Stock
10X	0.28	355, 532	20.00	378-809- 5	30.5	#86-176	C\$5,502.00	1 In Stock
20X	0.40	355, 532	10.00	378-817- 8	17.0	#46-407	C\$11,256.00	17 In Stock
50X	0.42	355, 532	4.00	378-818- 8	15.0	#46-408	C\$11,256.00	3 In Stock
100X	0.50	355, 532	2.00	378-819- 15	11.0	#46-409	C\$13,846.00	Contact Us
50X	0.65	355, 532	4.00	378-888- 6	10.0	#86-177	C\$22,960.00	Contact Us
10X	0.25	266, 355, 532	20.00	378-844- 15	20.0	#86-175	C\$19,460.00	Contact Us
20X	0.36	266, 532	10.00	378-837- 8	15.0	#56-320	C\$29,680.00	Contact Us
50X	0.40	266, 532	4.00	378-838- 8	12.0	#56-321	C\$30,380.00	Contact Us

80X	0.55	266, 532	2.50	378-839- 5	10.0	#56-322	C\$41,720.00	Contact Us
#75-053 New								
								
New								
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
100X	0.70	532, 1064	2.00	378-864- 5	10.00		C\$17,885.00	2 In Stock