

[All Products](#) / [Lasers](#) / [Laser Measurement and Electronics](#) / [Infrared \(IR\) and Ultraviolet \(UV\) Viewers](#)

ZAP-IT® Laser Alignment Paper



- Industrial Standard Beam Profile Viewing Paper
- Records Beam Shape, Divergence, Mode, and Intensity Profile of Pulsed Lasers
- Suitable for Broadband Sources from UV to IR

Common Specifications

General

Note:

Recommended Pulsed Width: 1ns to 30ms

Recommended Power Level Range: 5 mJ/cm² to 20 J/cm²

Physical & Mechanical Properties

Thickness (inches):	0.009
---------------------	-------

Thickness (mm):	0.24
-----------------	------

Technical Information

Products

Title	Stock Number	Price	Buy
ZAP-IT® Laser Alignment Paper, 2 x 5", Box of 20 Sheets	#15-825	C\$83.79 Volume Pricing	11 In Stock
ZAP-IT® Laser Alignment Paper, 2 x 5", Box of 50 Sheets	#15-826	C\$176.40 Volume Pricing	8 In Stock
ZAP-IT® Laser Alignment Paper, 4 x 8", Box of 20 Sheets	#15-824	C\$152.88 Volume Pricing	7 In Stock
ZAP-IT® Laser Alignment Paper, 4 x 8", Box of 50 Sheets	#90-709	C\$274.89	20+ In Stock
ZAP-IT® Laser Alignment Paper, 4 x 8", 2mm Sq. Grid Pattern, Box of 20 Sheets	#15-827	C\$176.40 Volume Pricing	3 In Stock
ZAP-IT® Laser Alignment Paper, 4 x 8", 2mm Sq. Grid Pattern, Box of 50 Sheets	#15-828	C\$291.06 Volume Pricing	3 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com