

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Cylinder Lenses](#) / [Laser Grade Cylinder Lenses](#)

TECHSPEC® Laser Grade Broadband Cylinder Lenses



- Offers Superior Performance from UV to IR
- Fused Silica Substrate
- Laser Optic Surface Quality

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Center Thickness Tolerance (mm):	±0.1
Dimensional Tolerance (mm):	+0.0/-0.025	Axial Twist (arcmin):	<3

Optical Properties

Substrate:	Fused Silica (Corning 7980)	Surface Quality:	20-10
Power (P-V) @ 632.8nm:	1.5λ	Irregularity (P-V) @ 632.8nm:	λ/4

Technical Information

Products

Dimensions (mm)	EFL (mm)	Substrate	Coating	Stock Number	Price	Buy
12.7 x 12.7	25.00	Fused Silica	Uncoated	#13-469	C\$208.25 Volume Pricing	20+ In Stock
12.7 x 12.7	50.00	Fused Silica	Uncoated	#36-089	C\$208.25 Volume Pricing	20+ In Stock
12.7 x 12.7	50.00	Fused Silica	UV-VIS (250-700nm)	#36-107	C\$271.56 Volume Pricing	Contact Us
12.7 x 12.7	50.00	Fused Silica	VIS 0° (425-675nm)	#36-098	C\$271.56 Volume Pricing	5 In Stock
12.7 x 12.7	50.00	Fused Silica	NIR I (600-1050nm)	#36-116	C\$271.56 Volume Pricing	1 In Stock
12.7 x 12.7	-25.00	Fused Silica	Uncoated	#13-468	C\$208.25 Volume Pricing	20+ In Stock
12.7 x 12.7	-50.00	Fused Silica	Uncoated	#36-094	C\$208.25 Volume Pricing	20+ In Stock
12.7 x 12.7	-50.00	Fused Silica	UV-VIS (250-700nm)	#36-112	C\$271.56 Volume Pricing	Contact Us
12.7 x 12.7	-50.00	Fused Silica	VIS 0° (425-675nm)	#36-103	C\$271.56 Volume Pricing	2 In Stock
12.7 x 12.7	-50.00	Fused Silica	NIR I (600-1050nm)	#36-122	C\$271.56 Volume Pricing	5 In Stock
12.7 x 12.7	150.00	Fused Silica	Uncoated	#13-471	C\$208.25 Volume Pricing	20+ In Stock
25.4 x 25.4	50.00	Fused Silica	Uncoated	#36-090	C\$244.90 Volume Pricing	20+ In Stock
25.4 x 25.4	50.00	Fused Silica	UV-VIS (250-700nm)	#36-108	C\$308.21 Volume Pricing	Contact Us
25.4 x 25.4	50.00	Fused Silica	VIS 0° (425-675nm)	#36-099	C\$308.21 Volume Pricing	Contact Us
25.4 x 25.4	50.00	Fused Silica	NIR I (600-1050nm)	#36-117	C\$308.21 Volume Pricing	2 In Stock

25.4 x 25.4	-50.00	Fused Silica	Uncoated	#36-095	C\$244.90 Volume Pricing	20+ In Stock
25.4 x 25.4	-50.00	Fused Silica	UV-VIS (250-700nm)	#36-113	C\$308.21 Volume Pricing	9 In Stock
25.4 x 25.4	-50.00	Fused Silica	VIS 0° (425-675nm)	#36-104	C\$308.21 Volume Pricing	4 In Stock
25.4 x 25.4	-50.00	Fused Silica	NIR I (600-1050nm)	#36-123	C\$308.21 Volume Pricing	3 In Stock
25.4 x 25.4	75.00	Fused Silica	Uncoated	#36-091	C\$244.90 Volume Pricing	20+ In Stock
25.4 x 25.4	75.00	Fused Silica	UV-VIS (250-700nm)	#36-109	C\$308.21 Volume Pricing	2 In Stock
25.4 x 25.4	75.00	Fused Silica	VIS 0° (425-675nm)	#36-100	C\$308.21 Volume Pricing	17 In Stock
25.4 x 25.4	75.00	Fused Silica	NIR I (600-1050nm)	#36-118	C\$308.21 Volume Pricing	4 In Stock
25.4 x 25.4	-75.00	Fused Silica	Uncoated	#36-096	C\$244.90 Volume Pricing	20+ In Stock
25.4 x 25.4	-75.00	Fused Silica	UV-VIS (250-700nm)	#36-114	C\$308.21 Volume Pricing	2 In Stock
25.4 x 25.4	-75.00	Fused Silica	VIS 0° (425-675nm)	#36-105	C\$308.21 Volume Pricing	1 In Stock
25.4 x 25.4	-75.00	Fused Silica	NIR I (600-1050nm)	#36-129	C\$308.21 Volume Pricing	4 In Stock
25.4 x 25.4	100.00	Fused Silica	Uncoated	#36-092	C\$244.90 Volume Pricing	20+ In Stock
25.4 x 25.4	100.00	Fused Silica	UV-VIS (250-700nm)	#36-110	C\$308.21 Volume Pricing	1 In Stock
25.4 x 25.4	100.00	Fused Silica	VIS 0° (425-675nm)	#36-101	C\$308.21 Volume Pricing	13 In Stock
25.4 x 25.4	100.00	Fused Silica	NIR I (600-1050nm)	#36-119	C\$308.21 Volume Pricing	9 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com