

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® Liquid Lens Cx Series Fixed Focal Length Lenses



- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Liquid Lens Provides Dynamic Autofocus
- 12mm to 50mm Focal Length

Common Specifications

General

Series: LL Cx Series

Physical & Mechanical Properties

Iris Option: Fixed

Optical Properties

Coating Specification: 425 - 675nm BBAR

Sensor

Pixel Size (µm): 2.74

Threading & Mounting

Filter Thread: M25.5 x 0.50 (Male)

Mount: C-Mount

Environmental & Durability Factors

Storage Temperature (°C): [-20 to +60](#)

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
12.00	1/2"	f/6	100 - ∞	C- Mount	#33-632	C\$726.11	7 In Stock
16.00	2/3"	f/5	100 - ∞	C- Mount	#33-646	C\$726.11	Contact Us
25.00	2/3"	f/5	150 - ∞	C- Mount	#33-661	C\$726.11	Contact Us
35.00	2/3"	f/7	225 - ∞	C- Mount	#33-677	C\$726.11	Contact Us
35.00	2/3"	f/5	225 - ∞	C- Mount	#33-676	C\$767.97	Contact Us
50.00	2/3"	f/7	250 - ∞	C- Mount	#33-687	C\$893.55	3 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com