

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Laser Mirrors](#)

TECHSPEC® Nd:YAG Laser Line Mirrors



- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

Common Specifications
Optical Properties

Surface Quality:	10-5	Surface Flatness (P-V):	$\lambda/10$
Coating Type:	Dielectric	Substrate:	Fused Silica (Corning 7980)

Technical Information

Products

Wavelength Range (nm)	DWL (nm)	Dia. (mm)	Dimensions (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
263 - 268	266	6.35	-	4.00	45	#38-829	C\$90.53 C\$181.05 Volume Pricing	14 In Stock
263 - 268	266	12.50	-	6.00	45	#47-980	C\$200.34 Volume Pricing	3 In Stock
263 - 268	266	12.70	-	6.35	45	#34-813	C\$200.34 Volume Pricing	Contact Us
263 - 268	266	19.10	-	6.35	45	#34-814	C\$218.15 Volume Pricing	4 In Stock
263 - 268	266	25.00	-	6.00	45	#47-981	C\$235.96 Volume Pricing	8 In Stock
263 - 268	266	25.40	-	6.35	45	#34-815	C\$235.96 Volume Pricing	2 In Stock
263 - 268	266	38.10	-	6.35	45	#34-816	C\$278.99 Volume Pricing	Contact Us
263 - 268	266	50.00	-	10.00	45	#63-116	C\$425.91 Volume Pricing	12 In Stock
263 - 268	266	50.80	-	9.53	45	#38-831	C\$425.91 Volume Pricing	5 In Stock
263 - 268	266	-	12.7 x 12.7	6.35	45	#39-581	C\$207.76 Volume Pricing	3 In Stock
263 - 268	266	-	19.1 x 12.7	6.35	45	#39-582	C\$218.15 Volume Pricing	8 In Stock
263 - 268	266	-	25.4 x 25.4	6.35	45	#39-583	C\$243.38 Volume Pricing	11 In Stock
263 - 268	266	-	38.1 x 25.4	6.35	45	#39-585	C\$250.80 Volume Pricing	Contact Us
263 - 268	266	-	6.35 x 6.35	3.18	45	#39-576	C\$191.44 Volume Pricing	13 In Stock

[#39-579 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

263 - 268	266	-	9.53 x 6.35	3.18	45		C\$64.52 C\$129.03	6 In Stock
-----------	-----	---	-------------	------	----	--	-------------------------------	------------

[#63-110 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

255 - 275	266	12.50	-	6.00	0		C\$35.58 C\$71.16	9 In Stock
-----------	-----	-------	---	------	---	--	------------------------------	------------

263 - 268	266	4.00	-	3.00	0-45	#12-623	C\$86.07 C\$172.14 Volume Pricing	14 In Stock
-----------	-----	------	---	------	------	-------------------------	---	-------------

263 - 268	266	6.35	-	4.00	0-45	#38-832	C\$200.34 Volume Pricing	20+ In Stock
-----------	-----	------	---	------	------	-------------------------	---	--------------

-	266	12.50	-	6.00	0-45	#88-523	C\$218.15 Volume Pricing	Contact Us
---	-----	-------	---	------	------	-------------------------	---	------------

263 - 268	266	12.70	-	6.35	0-45	#38-833	C\$218.15 Volume Pricing	3 In Stock
-----------	-----	-------	---	------	------	-------------------------	---	------------

263 - 268	266	19.10	-	6.35	0-45	#38-834	C\$235.96 Volume Pricing	20+ In Stock
-	266	25.00	-	6.00	0-45	#88-524	C\$250.80 Volume Pricing	20+ In Stock
263 - 268	266	25.40	-	6.35	0-45	#38-835	C\$250.80 Volume Pricing	20+ In Stock
263 - 268	266	38.10	-	6.35	0-45	#38-838	C\$293.83 Volume Pricing	2 In Stock
-	266	50.00	-	10.00	0-45	#88-525	C\$442.23 Volume Pricing	5 In Stock
263 - 268	266	50.80	-	9.53	0-45	#38-841	C\$442.23 Volume Pricing	8 In Stock
-	266	76.20	-	12.70	0-45	#20-418	C\$1,093.71 Volume Pricing	Contact Us
-	266	-	12.7 x 12.7	6.35	0-45	#39-589	C\$113.53 C\$227.06 Volume Pricing	12 In Stock
-	266	-	19.1 x 12.7	6.35	0-45	#39-590	C\$235.96 Volume Pricing	5 In Stock
-	266	-	25.4 x 25.4	6.35	0-45	#39-591	C\$259.70 Volume Pricing	3 In Stock
-	266	-	38.1 x 25.4	6.35	0-45	#39-592	C\$270.09 Volume Pricing	1 In Stock
-	266	-	6.35 x 6.35	3.18	0-45	#39-586	C\$207.76 Volume Pricing	14 In Stock

[#39-587 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

-	266	-	9.53 x 6.35	3.18	0-45		C\$70.46 C\$140.91	3 In Stock
351 - 358	355	6.35	-	4.00	45	#38-858	C\$181.05 Volume Pricing	7 In Stock

351 - 358	355	12.50	-	6.00	45	#47-323	C\$200.34 Volume Pricing	Contact Us
351 - 358	355	12.70	-	6.35	45	#34-818	C\$100.17 C\$200.34 Volume Pricing	2 In Stock
351 - 358	355	19.10	-	6.35	45	#34-819	C\$218.15 Volume Pricing	20+ In Stock
351 - 358	355	25.00	-	6.00	45	#47-324	C\$235.96 Volume Pricing	20+ In Stock
351 - 358	355	25.40	-	6.35	45	#34-820	C\$235.96 Volume Pricing	20+ In Stock
351 - 358	355	38.10	-	6.35	45	#34-821	C\$278.99 Volume Pricing	7 In Stock
351 - 358	355	50.00	-	10.00	45	#63-117	C\$425.91 Volume Pricing	10 In Stock
351 - 358	355	50.80	-	9.53	45	#38-862	C\$425.91 Volume Pricing	20+ In Stock
351 - 358	355	-	12.7 x 12.7	6.35	45	#39-616	C\$207.76 Volume Pricing	12 In Stock
351 - 358	355	-	19.1 x 12.7	6.35	45	#39-617	C\$218.15 Volume Pricing	20+ In Stock
351 - 358	355	-	25.4 x 25.4	6.35	45	#39-618	C\$243.38 Volume Pricing	4 In Stock
351 - 358	355	-	38.1 x 25.4	6.35	45	#39-619	C\$250.80 Volume Pricing	5 In Stock
351 - 358	355	-	6.35 x 6.35	3.18	45	#39-611	C\$191.44 Volume Pricing	7 In Stock

[#39-615 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

351 - 358	355	-	9.53 x 6.35	3.18	45		C\$64.52 C\$129.03	1 In Stock
-----------	-----	---	-------------	------	----	--	-------------------------------	------------

351 - 358	355	4.00	-	3.00	0-45	#12-625	C\$172.14 Volume Pricing	15 In Stock
351 - 358	355	6.35	-	4.00	0-45	#38-863	C\$200.34 Volume Pricing	20+ In Stock
-	355	12.50	-	6.00	0-45	#88-526	C\$109.08 C\$218.15 Volume Pricing	20+ In Stock
351 - 358	355	12.70	-	6.35	0-45	#38-864	C\$109.08 C\$218.15 Volume Pricing	20+ In Stock
351 - 358	355	19.10	-	6.35	0-45	#38-865	C\$117.98 C\$235.96 Volume Pricing	20+ In Stock
-	355	25.00	-	6.00	0-45	#88-527	C\$250.80 Volume Pricing	Contact Us
351 - 358	355	25.40	-	6.35	0-45	#38-866	C\$150.48 C\$250.80 Volume Pricing	20+ In Stock
351 - 358	355	38.10	-	6.35	0-45	#38-868	C\$293.83 Volume Pricing	9 In Stock
-	355	50.00	-	10.00	0-45	#88-528	C\$221.12 C\$442.23 Volume Pricing	2 In Stock
351 - 358	355	50.80	-	9.53	0-45	#38-870	C\$442.23 Volume Pricing	3 In Stock
-	355	76.20	-	12.70	0-45	#20-420	C\$1,093.71 Volume Pricing	9 In Stock
-	355	-	12.7 x 12.7	6.35	0-45	#39-622	C\$227.05 Volume Pricing	5 In Stock
-	355	-	19.1 x 12.7	6.35	0-45	#39-623	C\$235.96 Volume Pricing	6 In Stock
-	355	-	25.4 x 25.4	6.35	0-45	#39-624	C\$259.70 Volume Pricing	1 In Stock
-	355	-	38.1 x 25.4	6.35	0-45	#39-625	C\$135.05 C\$270.09 Volume Pricing	5 In Stock
-	355	-	6.35 x 6.35	3.18	0-45	#39-620	C\$207.76 Volume Pricing	5 In Stock

[#39-621 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

- 355 - 9.53 x 6.35 3.18 0-45 C\$70.46 ~~C\$140.91~~ 10 In Stock

523 - 537	532	6.35	-	4.00	45	#38-887	C\$181.05 Volume Pricing	3 In Stock
523 - 537	532	12.50	-	6.00	45	#45-990	C\$200.34 Volume Pricing	20+ In Stock
523 - 537	532	12.70	-	6.35	45	#34-823	C\$120.20 C\$200.34 Volume Pricing	20+ In Stock
523 - 537	532	19.10	-	6.35	45	#34-824	C\$218.15 Volume Pricing	17 In Stock
523 - 537	532	25.00	-	6.00	45	#45-991	C\$235.96 Volume Pricing	20+ In Stock
523 - 533	532	25.40	-	6.35	45	#34-825	C\$235.96 Volume Pricing	20+ In Stock
523 - 537	532	38.10	-	6.35	45	#34-826	C\$278.99 Volume Pricing	5 In Stock
523 - 537	532	50.00	-	10.00	45	#47-157	C\$425.91 Volume Pricing	20+ In Stock
523 - 537	532	50.80	-	9.53	45	#38-889	C\$425.91 Volume Pricing	20+ In Stock
-	532	76.20	-	12.70	0-45	#20-422	C\$1,093.71 Volume Pricing	5 In Stock
523 - 537	532	-	12.7 x 12.7	6.35	45	#39-641	C\$207.76 Volume Pricing	4 In Stock
523 - 537	532	-	19.1 x 12.7	6.35	45	#39-642	C\$218.15 Volume Pricing	20+ In Stock
523 - 537	532	-	25.4 x 25.4	6.35	45	#39-643	C\$243.38 Volume Pricing	3 In Stock
523 - 537	532	-	38.1 x 25.4	6.35	45	#39-644	C\$250.80 Volume Pricing	5 In Stock

523 - 537	532	-	6.35 x 6.35	3.18	45	#39-639	C\$191.44 Volume Pricing	9 In Stock
#39-640 Clearance								
 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
523 - 537	532	-	9.53 x 6.35	3.18	45		C\$64.52 C\$129.03	2 In Stock
523 - 537	532	4.00	-	3.00	0-45	#12-627	C\$172.14 Volume Pricing	Contact Us
523 - 537	532	6.35	-	4.00	0-45	#38-890	C\$200.34 Volume Pricing	9 In Stock
-	532	12.50	-	6.00	0-45	#88-529	C\$109.08 C\$218.15 Volume Pricing	20+ In Stock
523 - 537	532	12.70	-	6.35	0-45	#38-891	C\$218.15 Volume Pricing	20+ In Stock
523 - 537	532	19.10	-	6.35	0-45	#38-892	C\$235.96 Volume Pricing	14 In Stock
-	532	25.00	-	6.00	0-45	#88-530	C\$250.80 Volume Pricing	4 In Stock
523 - 537	532	25.40	-	6.35	0-45	#38-893	C\$250.80 Volume Pricing	20+ In Stock
523 - 537	532	38.10	-	6.35	0-45	#38-895	C\$146.92 C\$293.83 Volume Pricing	3 In Stock
-	532	50.00	-	10.00	0-45	#88-531	C\$442.23 Volume Pricing	4 In Stock
523 - 537	532	50.80	-	9.53	0-45	#38-897	C\$442.23 Volume Pricing	20+ In Stock
-	532	-	12.7 x 12.7	6.35	0-45	#39-647	C\$113.53 C\$227.05 Volume Pricing	7 In Stock
-	532	-	19.1 x 12.7	6.35	0-45	#39-648	C\$235.96 Volume Pricing	5 In Stock

-	532	-	25.4 x 25.4	6.35	0-45	#39-649	C\$259.70 Volume Pricing	13 In Stock
-	532	-	38.1 x 25.4	6.35	0-45	#39-650	C\$67.52 C\$270.09 Volume Pricing	10 In Stock
-	532	-	6.35 x 6.35	3.18	0-45	#39-645	C\$207.76 Volume Pricing	20+ In Stock

[#39-646 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

-	532, 1064	50.00	-	10.00	45	#63-118	C\$421.46 Volume Pricing	15 In Stock
1046 - 1074	1064	19.05	-	9.53	0	#17-624	C\$108.33 C\$216.66 Volume Pricing	Contact Us
1046 - 1074	1064	6.35	-	4.00	45	#38-898	C\$181.05 Volume Pricing	7 In Stock
1046 - 1074	1064	12.50	-	6.00	45	#45-986	C\$120.20 C\$200.34 Volume Pricing	20+ In Stock
1046 - 1074	1064	12.70	-	6.35	45	#34-828	C\$200.34 Volume Pricing	Contact Us
1046 - 1074	1064	19.10	-	6.35	45	#34-829	C\$218.15 Volume Pricing	3 In Stock
1046 - 1074	1064	25.00	-	6.00	45	#45-987	C\$235.96 Volume Pricing	20+ In Stock
1046 - 1074	1064	25.40	-	6.35	45	#34-830	C\$235.96 Volume Pricing	20+ In Stock
1046 - 1074	1064	38.10	-	6.35	45	#34-831	C\$278.99 Volume Pricing	20+ In Stock
1046 - 1074	1064	50.00	-	10.00	45	#47-156	C\$425.91 Volume Pricing	20+ In Stock

1046 - 1074	1064	50.80	-	9.53	45	#38-900	C\$425.91 Volume Pricing	20+ In Stock
-	1064	76.20	-	12.70	0-45	#20-430	C\$1,093.71 Volume Pricing	20+ In Stock
1046 - 1074	1064	-	12.7 x 12.7	6.35	45	#39-653	C\$207.76 Volume Pricing	6 In Stock
1046 - 1074	1064	-	19.1 x 12.7	6.35	45	#39-654	C\$218.15 Volume Pricing	1 In Stock
1046 - 1074	1064	-	25.4 x 25.4	6.35	45	#39-655	C\$243.38 Volume Pricing	13 In Stock
1046 - 1074	1064	-	38.1 x 25.4	6.35	45	#39-656	C\$250.80 Volume Pricing	6 In Stock
1046 - 1074	1064	-	6.35 x 6.35	3.18	45	#39-651	C\$191.44 Volume Pricing	5 In Stock
1046 - 1074	1064	4.00	-	3.00	0-45	#12-629	C\$172.14 Volume Pricing	5 In Stock
1046 - 1074	1064	6.35	-	4.00	0-45	#38-901	C\$50.09 C\$200.34 Volume Pricing	8 In Stock
-	1064	12.50	-	6.00	0-45	#88-532	C\$218.15 Volume Pricing	20+ In Stock
1046 - 1074	1064	12.70	-	6.35	0-45	#38-902	C\$109.08 C\$218.15 Volume Pricing	Contact Us
1046 - 1074	1064	19.10	-	6.35	0-45	#38-904	C\$235.96 Volume Pricing	9 In Stock
-	1064	25.00	-	6.00	0-45	#88-533	C\$250.80 Volume Pricing	16 In Stock
1046 - 1074	1064	25.40	-	3.18	0-45	#14-340	C\$250.80 Volume Pricing	Contact Us
1046 - 1074	1064	25.40	-	6.35	0-45	#38-905	C\$150.48 C\$250.80 Volume Pricing	20+ In Stock
1046 - 1074	1064	38.10	-	6.35	0-45	#38-907	C\$293.83 Volume Pricing	11 In Stock
-	1064	50.00	-	10.00	0-45	#88-534	C\$265.34 C\$442.23 Volume Pricing	7 In Stock
1046 - 1074	1064	50.80	-	9.53	0-45	#38-909	C\$442.23 Volume Pricing	20+ In Stock
-	1064	-	12.7 x 12.7	6.35	0-45	#39-659	C\$227.05 Volume Pricing	20+ In Stock
-	1064	-	19.1 x 12.7	6.35	0-45	#39-660	C\$235.96 Volume Pricing	5 In Stock
-	1064	-	25.4 x 25.4	6.35	0-45	#39-661	C\$129.85 C\$250.70 Volume Pricing	8 In Stock

-	1064	-	38.1 x 25.4	6.35	0-45	#39-662	C\$270.09 Volume Pricing	20+ In Stock
-	1064	-	6.35 x 6.35	3.18	0-45	#39-657	C\$207.76 Volume Pricing	20+ In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA
 Phone: 1-800-363-1992 :
www.edmundoptics.com