

[All Products](#) /
 [Optics](#) /
 [Optical Mirrors](#) /
 [Flat Mirrors](#) /
 [Laser Mirrors](#)

TECHSPEC® Dual Band Laser Line Mirrors



- >99% Reflectivity at Design Wavelengths
- 10-5 Surface Quality for Sensitive Laser Applications
- 532/1064nm, 635-670/1064nm, or 800/1030nm Wavelength Bands
- [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%):	>90
---------------------	-----

Optical Properties

Surface Quality:	10-5
------------------	------

Surface Flatness (P-V):	$\lambda/10$
-------------------------	--------------

Coating Type:	Dielectric
---------------	------------

Substrate:	Fused Silica (Corning 7980)
------------	---

Technical Information

Products

DWL (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
532, 1064	12.50	3.00	45	#20-371	C\$216.66 Volume Pricing	Contact Us
532, 1064	12.50	6.00	45	#47-976	C\$216.66 Volume Pricing	13 In Stock
532, 1064	12.70	6.35	45	#28-974	C\$258.22 Volume Pricing	8 In Stock
532, 1064	25.00	3.00	45	#20-216	C\$247.83 Volume Pricing	20+ In Stock
532, 1064	25.00	6.00	45	#47-977	C\$247.83 Volume Pricing	16 In Stock
532, 1064	25.40	6.35	45	#28-975	C\$295.32 Volume Pricing	10 In Stock
532, 1064	50.00	10.00	45	#63-118	C\$421.46 Volume Pricing	15 In Stock
532, 1064	50.80	9.53	45	#28-976	C\$501.59 Volume Pricing	4 In Stock
532, 1064	76.20	12.70	45	#27-037	C\$1,075.90 Volume Pricing	6 In Stock
532, 1064	50.80	6.35	45	#20-612	C\$421.46 Volume Pricing	7 In Stock
532, 635, 650, 1064	12.70	6.35	45	#26-926	C\$243.38 Volume Pricing	8 In Stock
532, 635, 650, 1064	12.70	6.35	0 - 45	#28-980	C\$289.38 Volume Pricing	7 In Stock
532, 635, 650, 1064	25.40	6.35	45	#26-927	C\$276.02 Volume Pricing	20+ In Stock
532, 635, 650, 1064	25.40	6.35	0 - 45	#28-981	C\$330.93 Volume Pricing	20+ In Stock
532, 635, 650, 1064	50.80	9.53	45	#26-928	C\$471.91 Volume Pricing	12 In Stock
532, 635, 650, 1064	50.80	9.53	0 - 45	#28-982	C\$562.44 Volume Pricing	9 In Stock
635, 670, 1064	12.50	3.00	45	#20-399	C\$216.66 Volume Pricing	Contact Us

635, 670, 1064	12.50	6.00	45	#47-978	C\$216.66 Volume Pricing	20+ In Stock
635, 670, 1064	12.70	6.35	45	#28-977	C\$258.22 Volume Pricing	5 In Stock
635, 670, 1064	25.00	3.00	45	#20-599	C\$247.83 Volume Pricing	20+ In Stock
635, 670, 1064	25.00	6.00	45	#47-979	C\$247.83 Volume Pricing	20+ In Stock
635, 670, 1064	25.40	6.35	45	#28-978	C\$295.32 Volume Pricing	17 In Stock
635, 670, 1064	50.00	10.00	45	#63-119	C\$421.46 Volume Pricing	14 In Stock
635, 670, 1064	50.80	6.35	45	#20-607	C\$421.46 Volume Pricing	14 In Stock
635, 670, 1064	50.80	9.53	45	#28-979	C\$501.59 Volume Pricing	1 In Stock
635, 670, 1064	76.20	12.70	45	#27-038	C\$1,075.90 Volume Pricing	4 In Stock
800, 1030	12.70	6.35	45	#28-965	C\$258.22 Volume Pricing	9 In Stock
800, 1030	12.70	6.35	0 - 45	#28-968	C\$310.16 Volume Pricing	9 In Stock
800, 1030	25.40	6.35	45	#28-966	C\$295.32 Volume Pricing	20+ In Stock
800, 1030	25.40	6.35	0 - 45	#28-969	C\$356.16 Volume Pricing	20+ In Stock
800, 1030	50.80	9.53	45	#28-967	C\$501.59 Volume Pricing	5 In Stock
800, 1030	50.80	9.53	0 - 45	#28-970	C\$592.12 Volume Pricing	5 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA
Phone: 1-800-363-1992 :
www.edmundoptics.com