

[All Products](#) / [Optics](#) / [Fiber Optics](#)

Single Mode Fiber Optic Patchcords



- FC/PC, FC/APC, and Hybrid Terminated Connectors
- Patchcords for Wavelengths from 450 – 1650nm
- 1m, 2m and 5m Standardized Lengths Available

Common Specifications

Physical & Mechanical Properties

Jacket Material:

900µm Yellow Hytrel® Tubing

Optical Properties

Numerical Aperture NA:

0.13

Technical Information

Products

Wavelength Range (nm)	Mode Field Diameter (nm)	NA	Connector	Length (m)	Stock Number	Price	Buy
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	1	#25-928	C\$63.00 Volume Pricing	3 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	2	#25-929	C\$65.80 Volume Pricing	1 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	5	#71-136	C\$70.00 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	1	#25-930	C\$97.30 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	2	#25-931	C\$105.70 Volume Pricing	2 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	5	#71-137	C\$118.30 Volume Pricing	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	1	#25-932	C\$128.80 Volume Pricing	7 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	2	#25-933	C\$138.60 Volume Pricing	4 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	5	#71-138	C\$154.00 Volume Pricing	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC	1	#25-934	C\$101.50 Volume Pricing	Contact Us
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC	2	#25-935	C\$104.30 Volume Pricing	1 In Stock
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/PC	5	#71-139	C\$108.50 Volume Pricing	Contact Us
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC	1	#25-936	C\$114.10 Volume Pricing	1 In Stock

450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC	2	#25-937	C\$122.50 Volume Pricing	6 In Stock
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/PC	5	#71-140	C\$135.80 Volume Pricing	1 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	1	#25-938	C\$98.70 Volume Pricing	3 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	2	#25-939	C\$101.50 Volume Pricing	1 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	5	#71-141	C\$105.70 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	1	#25-940	C\$159.60 Volume Pricing	Contact Us
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	2	#25-941	C\$166.60 Volume Pricing	Contact Us
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	5	#71-142	C\$179.20 Volume Pricing	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	1	#25-942	C\$165.20 Volume Pricing	4 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	2	#25-943	C\$173.60 Volume Pricing	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	5	#71-143	C\$187.60 Volume Pricing	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/APC	1	#25-944	C\$134.40 Volume Pricing	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/APC	2	#25-945	C\$137.20 Volume Pricing	2 In Stock
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/APC	5	#71-144	C\$141.40 Volume Pricing	2 In Stock
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/APC	1	#25-946	C\$148.40 Volume Pricing	1 In Stock

450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/APC	2	#25-947	C\$154.00 Volume Pricing	1 In Stock
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/APC	5	#71-145	C\$162.40 Volume Pricing	2 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC to FC/APC	1	#25-948	C\$81.20 Volume Pricing	5 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC to FC/APC	5	#71-146	C\$88.20 Volume Pricing	5 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC to FC/APC	1	#25-949	C\$142.80 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC to FC/APC	5	#71-147	C\$163.80 Volume Pricing	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC to FC/APC	1	#25-950	C\$151.20 Volume Pricing	3 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC to FC/APC	5	#71-148	C\$176.40 Volume Pricing	3 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC to FC/APC	1	#25-951	C\$123.90 Volume Pricing	1 In Stock
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/PC to FC/APC	5	#71-149	C\$131.60 Volume Pricing	1 In Stock
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC to FC/APC	1	#25-952	C\$140.00 Volume Pricing	1 In Stock
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/PC to FC/APC	5	#71-150	C\$161.00 Volume Pricing	1 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA
Phone: 1-800-363-1992 :
www.edmundoptics.com