

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® UAV Series Fixed Focal Length Lenses





- Compact, Infinite Conjugate Lens Ideal for Photogrammetry
- 8mm, 12mm, 16mm, 25mm, and 35mm Focal Lengths
- 1.2", C-Mount Lens
- Up to 24.4 MegaPixels, 2.7 μ m Pixel Size Sensors

Common Specifications

General			
Imaging Lens Type:		Infinite Conjugate	
Physical & Mechanical Properties			
Iris Option:		Variable	
Optical Properties			
Maximum Image Circle (mm):		19.30	Wavelength Range (nm): 425 - 675
Working Distance (mm):		500 - ∞	Coating: 425 - 675 BBAR
Coating Specification:		425 - 675 BBAR	
Sensor			
Maximum Sensor Format:		1.2"	
Threading & Mounting			
Mount:		C-Mount	
Environmental & Durability Factors			
Storage Temperature (°C):		-20 to +60 For questions regarding operating temperature please contact our support team	

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
					#22-834 New		
							
					New		
8.00	1.2"	2.8 - 16	500 - ∞	C-Mount	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	C\$1,440.95	5 In Stock
					#22-835 New		
							
					New		
12.00	1.2"	2.8 - 16	500 - ∞	C-Mount	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	C\$1,378.30	8 In Stock
16.00	1.2"	f/2.8 - f/16	500 - ∞	C-Mount	#22-836	C\$1,440.95	14 In Stock

25.00	1.2"	f/2.8 - f/16	500 - ∞	C- Mount	#22-837	C\$1,440.95	5 In Stock
35.00	1.2"	f/2.8 - f/16	500 - ∞	C- Mount	#22-838	C\$1,440.95	20+ In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com