

19mm Diameter Sandblasted Glass



Stock **#43-721** 20+ In Stock

-

1

+

C\$40^{.81}

ADD TO CART

Volume Pricing	
Qty 1-10	C\$40.81 each
Qty 11+	C\$31.91 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Ground Glass Diffuser

Type:

Physical & Mechanical Properties

Diameter (mm):

19.00	
1.60	Thickness (mm):
Optical Properties	
Float Glass	Substrate: ☐
350 - 2000	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Large Sizes Available
- 120-Grit Sandblast
- Economically Priced

Commercial Quality Sandblasted Glass is finely etched on one side to allow improved light diffusion. With a 120-grit sandblast spray, it is ideal for use in rear projection screen systems.

COMPATIBLE MOUNTS