

TECHSPEC[®] 4.0mm Diameter x 8.0mm Length, N-BK7 Rod Lens



Stock #54-089 14 In Stock

-

1

+

C\$65^{.67}

ADD TO CART

Volume Pricing	
Qty 1-5	C\$65.67 each
Qty 6-25	C\$52.31 each
Qty 26-49	C\$49.34 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:
Rod Lens

Physical & Mechanical Properties

4.00 +0.00/-0.03	Diameter (mm):
8.00	Length (mm):
+0/-0.1	Length Tolerance (mm):
Optical Properties	
N-BK7	Substrate: ☐
Uncoated	Coating:
350 - 2200	Wavelength Range (nm):
40-20	Surface Quality:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

PRODUCT DETAILS

- Focuses Collimated Light into a Line
- Available in Diameters as Small as 1mm

TECHSPEC® Rod Lenses are polished on the circumference and ground on both ends. Optical performance is similar to a cylinder lens. Collimated light passing through the diameter of the rod lens will be focused into a line. TECHSPEC ® Rod Lenses are offered in diameters ranging from 1mm to 10mm.

TECHNICAL INFORMATION

Rod Lens

