

4.6" Blue Advanced Illumination High Intensity Ring Light

See More by [Advanced Illumination](#)



Stock **#88-488** [CONTACT US](#)

-

1

+

C\$1,204^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,204.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

Model Number:

RL127-470-IC

50,000	LED Lifetime (hours):
--------	-----------------------

1.00	Number of Channels:
------	---------------------

LED Illuminator	Type of Illumination:
-----------------	-----------------------

Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	
Advanced Illumination	Manufacturer:

Ring Light	Geometry:
------------	-----------

Constant	Illumination Mode:
----------	--------------------

Physical & Mechanical Properties	
----------------------------------	--

116.80	Diameter (mm):
--------	----------------

19.1	Height (mm):
------	--------------

M67 x0.75	Inner Diameter (mm):
-----------	----------------------

116.8	Outer Diameter (mm):
-------	----------------------

304.00	Weight (g):
--------	-------------

Optical Properties	
--------------------	--

Blue	Color:
------	--------

470.00	Wavelength (nm):
--------	------------------

100 - 300	Working Distance (mm):
-----------	------------------------

Hardware & Interface Connectivity	
-----------------------------------	--

Flying Leads	Connector:
--------------	------------

Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
--	--

Environmental & Durability Factors	
------------------------------------	--

0 to 60	Operating Temperature (°C):
---------	-----------------------------

IP67	Environmental Rating:
------	-----------------------

Regulatory Compliance	
-----------------------	--

Compliant	RoHS 2015:
---------------------------	------------

View	Certificate of Conformance:
----------------------	-----------------------------

Contains SVHC(s)	Reach 233:
----------------------------------	------------


PRODUCT DETAILS

- Slim Profile to Ease System Integration
- High Brightness LEDs
- Multiple Size, Wavelength, and Working Distance Options

Advanced Illumination High Intensity Ring Lights utilize an arrangement of high brightness LEDs to precisely illuminate a wide variety of imaging applications. Advanced Illumination High Intensity Ring Lights feature a slim profile to ease system integration, and are available in a variety of sizes, wavelengths, and working distance options. A manual intensity adjustment option is also available for added flexibility. 4.6" and 6" models are IP67 compliant. An adapter is also available for mounting the 2.95" ring light to M25 x0.5 lenses.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately.

3D-Printable Mount Files



Ring Light Configuration

**DOWNLOAD
NOW**

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications

[Read](#) 



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries

[Watch](#) 