

4'x8'x8" CleanTop Optical Table, English



Stock **#78-482** NEW CONTACT US

-

1

+

C\$19,292⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$19,292.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

English

Physical & Mechanical Properties

203.20	Thickness (mm):
8	Thickness (inches):
101.60	Length (mm):
203.20	Width (mm):
Construction: Top: Stainless Steel Core, All Steel, High Density, Cell-Sized Honeycomb Core Frame: Medium Texture Black Powder Coat	
60 - 80	Feed Pressure (psi):
±0.005	Flatness (inches):
Adjustable	Height (inches):
1287	Weight (lbs):
8	Width (ft):
4	Length (ft):

Threading & Mounting

1/4-20 on 1" Centerline	Mounting Threads:
-------------------------	-------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

PRODUCT DETAILS

- All Steel, Vacuum Compatible, Spill Proof Optical Top
- Available with English or Metric Tapped Holes
- Highest Core Density and Smallest Honeycomb Cell Area

TMC™ Vibration Control CleanTop® Performance Series Optical Tables feature a spill-proof all-steel construction, which adds structural integrity, thermal stability, and vacuum compatibility for laboratory or industrial environments. These tables feature either standard 1/4–20 on 1 in. centers tapped holes or metric M6 on 25 mm centers tapped holes and are available with casters for convenient installation or relocation. Each CleanTop cup is individually epoxied and the small cylindrical cell size of approximately 0.5 in., ensures a more stable working environment. TMC™ Vibration Control CleanTop® Performance Series Optical Tables feature a lightly sanded surface to reduce reflections from the optical top. These tables are ideal for applications requiring an extremely sensitive working environment, such as interferometry, holography, and ultra-fast laser metrology.

TECHNICAL INFORMATION



