

TECHSPEC®

1/4-20 Rotating Adapter Plate



Stock #55-210 20+ In Stock

-

1

+

C\$123^{.48}

ADD TO CART

Volume Pricing	
Qty 1-9	C\$123.48 each
Qty 10+	C\$109.37 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

English

Type:

Rotation

Function:

Physical & Mechanical Properties	
14.00	Thickness (mm):
32.0	Outer Diameter (mm):
Threading & Mounting	
1/4-20 Male, 1/4-20 Female	Mounting Threads:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

PRODUCT DETAILS

- Ideal for use with Post and Post Holder Applications
- Features 1/4-20 Male/Female Threads
- Rotates 360° and Includes Locking Set Screw

TECHNICAL INFORMATION

