

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)

TECHSPEC® $\lambda/4$ First Surface Mirrors



- Available in a Wide Range of Sizes and Shapes
- Precision Metallic Mirror Coatings
- [Contact Us](#) for Custom Sizes

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Edges:	Fine Ground
---------------	----------------------	---------------	-------------

Optical Properties

Surface Flatness (P-V):	$\lambda/4$	Substrate:	BOROFLOAT®
Surface Quality:	60-40	Coating Type:	Metal

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Coating Specification	Coating	Thickness (mm)	Stock Number	Price	Buy
5.00	λ/4	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#48-404	C\$77.91 Volume Pricing	20+ In Stock
5.00	λ/4	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#48-407	C\$77.91 Volume Pricing	Contact Us
5.00	λ/4	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#48-410	C\$101.65 Volume Pricing	20+ In Stock
5.00	λ/4	-	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-186	C\$93.49 Volume Pricing	1 In Stock
-	λ/4	5.0 x 5.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#48-405	C\$77.91 Volume Pricing	20+ In Stock
-	λ/4	5.0 x 5.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#48-408	C\$77.91 Volume Pricing	8 In Stock
-	λ/4	5.0 x 5.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#48-411	C\$101.65 Volume Pricing	8 In Stock
-	λ/4	5.0 x 5.0	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-187	C\$93.49 Volume Pricing	8 In Stock
10.00	λ/4	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#45-598	C\$77.91 Volume Pricing	Contact Us
10.00	λ/4	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#45-599	C\$77.91 Volume Pricing	Contact Us

10.00	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#45-600	C\$101.65 Volume Pricing	Contact Us
10.00	$\lambda/4$	-	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-188	C\$93.49 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#45-722	C\$77.91 Volume Pricing	13 In Stock
-	$\lambda/4$	10.0 x 10.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#45-723	C\$77.91 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#45-724	C\$101.65 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-189	C\$93.49 Volume Pricing	Contact Us
12.50	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#45-601	C\$77.91 Volume Pricing	20+ In Stock
12.50	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#45-602	C\$77.91 Volume Pricing	20+ In Stock
12.50	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#45-603	C\$101.65 Volume Pricing	5 In Stock
12.50	$\lambda/4$	-	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-190	C\$93.49 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 12.5	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#48-406	C\$77.91 Volume Pricing	Contact Us

-	$\lambda/4$	12.5 x 12.5	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#48-409	C\$77.91 Volume Pricing	14 In Stock
-	$\lambda/4$	12.5 x 12.5	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#48-412	C\$101.65 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 12.5	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-191	C\$93.49 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 17.5	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#25-746	C\$81.62 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 17.5	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#25-747	C\$81.62 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 17.5	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#25-748	C\$109.07 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 17.5	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#25-749	C\$101.65 Volume Pricing	7 In Stock
12.70	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#25-730	C\$77.91 Volume Pricing	Contact Us
12.70	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#25-731	C\$77.91 Volume Pricing	6 In Stock
12.70	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#25-732	C\$101.65 Volume Pricing	1 In Stock
12.70	$\lambda/4$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#25-733	C\$93.49 Volume Pricing	Contact Us

15.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#63-162	C\$81.62 Volume Pricing	20+ In Stock
15.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#63-168	C\$81.62 Volume Pricing	Contact Us
15.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#63-174	C\$109.07 Volume Pricing	20+ In Stock
15.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#88-535	C\$101.65 Volume Pricing	Contact Us
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-725	C\$81.62 Volume Pricing	20+ In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-726	C\$81.62 Volume Pricing	Contact Us
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-727	C\$109.07 Volume Pricing	20+ In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-192	C\$101.65 Volume Pricing	Contact Us
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#30-875	C\$70.49 Volume Pricing	20+ In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#43-506	C\$81.62 Volume Pricing	7 In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#46-716	C\$81.62 Volume Pricing	12 In Stock

-	$\lambda/4$	16.0 x 23.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-432	C\$109.07 Volume Pricing	16 In Stock
-	$\lambda/4$	16.0 x 23.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-721	C\$101.65 Volume Pricing	20+ In Stock
20.00	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#63-163	C\$86.07 Volume Pricing	20+ In Stock
20.00	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#63-169	C\$86.07 Volume Pricing	Contact Us
20.00	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#63-175	C\$112.78 Volume Pricing	2 In Stock
20.00	$\lambda/4$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#88-536	C\$105.36 Volume Pricing	5 In Stock
-	$\lambda/4$	20.0 x 20.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#45-728	C\$86.07 Volume Pricing	5 In Stock
-	$\lambda/4$	20.0 x 20.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#45-729	C\$86.07 Volume Pricing	7 In Stock
-	$\lambda/4$	20.0 x 20.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#45-730	C\$112.78 Volume Pricing	20+ In Stock
-	$\lambda/4$	20.0 x 20.0	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#49-193	C\$105.36 Volume Pricing	Contact Us
-	$\lambda/4$	21.0 x 30.0	R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm	Protected Aluminum (400- 2000nm)	5.00	#32-454	C\$74.20 Volume Pricing	Contact Us

-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#43-507	C\$86.07 Volume Pricing	20+ In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#46-717	C\$86.07 Volume Pricing	1 In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-742	C\$112.78 Volume Pricing	20+ In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-722	C\$105.36 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 85\% @$ 400 - 700nm $R_{avg} > 90\% @$ 400 - 2000nm	Protected Aluminum (400- 2000nm)	5.00	#33-510	C\$74.20 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#32-516	C\$86.07 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#46-718	C\$86.07 Volume Pricing	Contact Us
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-433	C\$112.78 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-723	C\$105.36 Volume Pricing	15 In Stock
25.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#45-604	C\$97.20 Volume Pricing	20+ In Stock
25.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#45-605	C\$97.20 Volume Pricing	Contact Us

25.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#45-606	C\$140.24 Volume Pricing	5 In Stock
25.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#49-194	C\$117.24 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#30-286	C\$81.62 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	6.00	#45-333	C\$97.20 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	6.00	#45-334	C\$97.20 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	6.00	#45-335	C\$140.24 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	6.00	#49-195	C\$117.24 Volume Pricing	3 In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#32-513	C\$97.20 Volume Pricing	Contact Us
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#46-719	C\$97.20 Volume Pricing	Contact Us
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#32-434	C\$140.24 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#46-724	C\$117.24 Volume Pricing	20+ In Stock

25.40	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#25-734	C\$97.20 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#25-735	C\$97.20 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#25-736	C\$140.24 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#25-737	C\$117.24 Volume Pricing	7 In Stock
30.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#63-164	C\$120.95 Volume Pricing	Contact Us
30.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#63-170	C\$120.95 Volume Pricing	9 In Stock
30.00	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#63-176	C\$163.24 Volume Pricing	20+ In Stock
30.00	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#88-537	C\$136.53 Volume Pricing	4 In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#63-165	C\$120.95 Volume Pricing	5 In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#63-171	C\$120.95 Volume Pricing	20+ In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#63-177	C\$163.24 Volume Pricing	5 In Stock

-	$\lambda/4$	30.0 x 30.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#88-538	C\$136.53 Volume Pricing	20+ In Stock
-	$\lambda/4$	35.0 x 50.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#25-750	C\$151.37 Volume Pricing	2 In Stock
-	$\lambda/4$	35.0 x 50.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#25-751	C\$151.37 Volume Pricing	5 In Stock
-	$\lambda/4$	35.0 x 50.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#25-752	C\$218.15 Volume Pricing	1 In Stock
-	$\lambda/4$	35.0 x 50.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#25-753	C\$179.56 Volume Pricing	7 In Stock
40.00	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	4.00	#63-166	C\$143.95 Volume Pricing	20+ In Stock
40.00	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	4.00	#63-172	C\$143.95 Volume Pricing	Contact Us
40.00	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	4.00	#63-178	C\$198.86 Volume Pricing	5 In Stock
40.00	$\lambda/4$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	4.00	#88-539	C\$160.27 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#63-167	C\$143.95 Volume Pricing	15 In Stock
-	$\lambda/4$	40.0 x 40.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#63-173	C\$143.95 Volume Pricing	20+ In Stock

-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#63-179	C\$198.86 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#88-540	C\$160.27 Volume Pricing	20+ In Stock
50.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#45-607	C\$163.24 Volume Pricing	14 In Stock
50.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	4.00	#45-608	C\$163.24 Volume Pricing	20+ In Stock
50.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	4.00	#45-609	C\$237.44 Volume Pricing	Contact Us
50.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	4.00	#49-196	C\$198.86 Volume Pricing	20+ In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	10.00	#45-336	C\$163.24 Volume Pricing	1 In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	10.00	#45-337	C\$163.24 Volume Pricing	8 In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	10.00	#45-338	C\$237.44 Volume Pricing	Contact Us
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	10.00	#49-197	C\$198.86 Volume Pricing	7 In Stock
50.80	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#25-738	C\$163.24 Volume Pricing	Contact Us

50.80	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	4.00	#25-739	C\$163.24 Volume Pricing	4 In Stock
50.80	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	4.00	#25-740	C\$237.44 Volume Pricing	7 In Stock
50.80	$\lambda/4$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	4.00	#25-741	C\$198.86 Volume Pricing	8 In Stock
51.00	$\lambda/4$	-	R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm	Protected Aluminum (400- 2000nm)	13.00	#33-511	C\$93.49 Volume Pricing	Contact Us
51.00	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	13.00	#32-514	C\$163.24 Volume Pricing	2 In Stock
51.00	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	13.00	#46-720	C\$163.24 Volume Pricing	2 In Stock
51.00	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	13.00	#32-435	C\$237.44 Volume Pricing	20+ In Stock
51.00	$\lambda/4$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	13.00	#46-725	C\$198.86 Volume Pricing	3 In Stock
-	$\lambda/4$	75.0 x 75.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	12.00	#45-339	C\$316.09 Volume Pricing	13 In Stock
-	$\lambda/4$	75.0 x 75.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	12.00	#45-340	C\$316.09 Volume Pricing	6 In Stock
-	$\lambda/4$	75.0 x 75.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	12.00	#45-341	C\$424.42 Volume Pricing	4 In Stock

-	$\lambda/4$	75.0 x 75.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450-10000nm)	12.00	#88-541	C\$366.55 Volume Pricing	20+ In Stock
-	$\lambda/4$	100.0 x 100.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450-650nm)	15.00	#45-342	C\$506.04 Volume Pricing	14 In Stock
-	$\lambda/4$	100.0 x 100.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250-700nm)	15.00	#45-343	C\$506.04 Volume Pricing	20+ In Stock
-	$\lambda/4$	100.0 x 100.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700-10000nm)	15.00	#45-344	C\$697.48 Volume Pricing	5 In Stock
			$R_{avg} > 98\% @$ 450 - 1000nm $R_{avg} > 98\% @$ 2000 - 10000nm	Protected Silver (450-10000nm)	15.00	#88-542	C\$537.21 Volume Pricing	9 In Stock

Copyright 2023, Edmund Optics Inc., 100 East Gloucester Pike, Barrington, NJ 08007-1380 USA
Phone: 1-800-363-1992 :
www.edmundoptics.com