



[All Products](#) / [Testing and Detection](#) / [Detectors](#)

Silicon Photodiodes



- UV Enhanced, Blue Enhanced, and Normal Response Options
- Active Areas from <1 to 100mm^2
- [C-Mount and S-Mount Mounting Solutions](#) Available

Technical Information



Products

Type	Note	Active Area (mm ²)	Package	Stock Number	Price	Buy
Biased	Normal Response	0.20	TO-18	#57-506	C\$53.90 Volume Pricing	5 In Stock
Biased	Normal Response	0.81	TO-18	#57-507	C\$53.90 Volume Pricing	12 In Stock
Biased	Normal Response	3.2	TO-18	#53-372	C\$53.90 Volume Pricing	5 In Stock
Biased	Normal Response	5.1	TO-5	#53-371	C\$69.65 Volume Pricing	Contact Us
Biased	Normal Response	16.4	TO-8	#54-034	C\$78.40 Volume Pricing	20+ In Stock
Biased	Normal Response	44.0	TO-8	#54-035	C\$107.80 Volume Pricing	17 In Stock
Biased	Normal Response	100.0	BNC	#53-373	C\$200.20 Volume Pricing	20+ In Stock
Biased	Normal Response	613.0	BNC	#53-374	C\$667.80 Volume Pricing	5 In Stock
Unbiased	Blue Enhanced Response	0.81	TO-18	#57-508	C\$69.65 Volume Pricing	20+ In Stock
Unbiased	Blue Enhanced Response	5.1	TO-5	#53-378	C\$69.65 Volume Pricing	20+ In Stock
Unbiased	Blue Enhanced Response	100.0	BNC	#53-379	C\$196.00 Volume Pricing	6 In Stock
Unbiased	UV Enhanced Response	15.0	TO-5	#57-510	C\$107.80 Volume Pricing	3 In Stock
Unbiased	UV Enhanced Response	20.0	TO-8	#54-036	C\$107.80 Volume Pricing	1 In Stock
Unbiased	UV Enhanced Response	35.0	TO-8	#54-037	C\$149.80 Volume Pricing	Contact Us
Unbiased	UV Enhanced Response	50.0	BNC	#53-376	C\$243.60 Volume Pricing	1 In Stock
Unbiased	UV Enhanced Response	100.0	BNC	#53-377	C\$289.80 Volume Pricing	Contact Us



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com