

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Longpass Filters](#)

Hoya Colored Glass Longpass Filters

See More by [Hoya](#)



- UV, VIS and IR Pass Ranges
- VIS Can Be Used for Color Bandpass
- Also Available [Mounted](#)

Common Specifications


Physical & Mechanical Properties

Bevel:	Protective as needed
--------	----------------------


Optical Properties

Substrate:	Colored Glass
Coating:	Uncoated

Technical Information



Hoya Colored Glass Longpass Filters



Products

Dimensions (mm)	Dia. (mm)	Glass/Filter Number	Cut-On Wavelength (nm)	Thickness (mm)	Stock Number	Price	Buy
-	12.50	Hoya UV28N	280.00	1.00	#18-791	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya UV28N	280.00	2.50	#18-792	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya UV28N	280.00	1.00	#18-793	C\$70.20 Volume Pricing	11 In Stock
-	25.40	Hoya UV28N	280.00	2.50	#18-794	C\$70.20 Volume Pricing	20+ In Stock
-	50.00	Hoya UV28N	280.00	1.00	#18-795	C\$140.39 Volume Pricing	7 In Stock
-	50.00	Hoya UV28N	280.00	2.50	#18-796	C\$140.39 Volume Pricing	7 In Stock
50.8 x 50.8	-	Hoya UV28N	280.00	1.00	#18-797	C\$140.39 Volume Pricing	5 In Stock
50.8 x 50.8	-	Hoya UV28N	280.00	2.50	#18-798	C\$140.39 Volume Pricing	2 In Stock
-	12.50	Hoya UV30N	300.00	1.00	#18-799	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya UV30N	300.00	2.50	#18-800	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya UV30N	300.00	1.00	#18-801	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya UV30N	300.00	2.50	#18-802	C\$70.20 Volume Pricing	20+ In Stock
-	50.00	Hoya UV30N	300.00	1.00	#18-803	C\$140.39 Volume Pricing	2 In Stock
-	50.00	Hoya UV30N	300.00	2.50	#18-804	C\$140.39 Volume Pricing	9 In Stock
50.8 x 50.8	-	Hoya UV30N	300.00	1.00	#18-805	C\$140.39 Volume Pricing	4 In Stock
50.8 x 50.8	-	Hoya UV30N	300.00	2.50	#18-806	C\$140.39 Volume Pricing	5 In Stock
-	12.50	Hoya UV32N	320.00	1.00	#18-807	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya UV32N	320.00	2.50	#18-808	C\$50.36 Volume Pricing	20+ In Stock

-	25.40	Hoya UV32N	320.00	1.00	#18-809	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya UV32N	320.00	2.50	#18-810	C\$70.20 Volume Pricing	20+ In Stock
-	50.00	Hoya UV32N	320.00	1.00	#18-811	C\$140.39 Volume Pricing	8 In Stock
-	50.00	Hoya UV32N	320.00	2.50	#18-812	C\$140.39 Volume Pricing	7 In Stock
50.8 x 50.8	-	Hoya UV32N	320.00	1.00	#18-813	C\$140.39 Volume Pricing	6 In Stock
50.8 x 50.8	-	Hoya UV32N	320.00	2.50	#18-814	C\$140.39 Volume Pricing	7 In Stock
-	12.50	Hoya UV34N	340.00	1.00	#18-815	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya UV34N	340.00	2.50	#18-816	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya UV34N	340.00	1.00	#18-817	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya UV34N	340.00	2.50	#18-818	C\$70.20 Volume Pricing	20+ In Stock
-	50.00	Hoya UV34N	340.00	1.00	#18-819	C\$140.39 Volume Pricing	5 In Stock
-	50.00	Hoya UV34N	340.00	2.50	#18-820	C\$140.39 Volume Pricing	Contact Us
50.8 x 50.8	-	Hoya UV34N	340.00	1.00	#18-821	C\$140.39 Volume Pricing	6 In Stock
50.8 x 50.8	-	Hoya UV34N	340.00	2.50	#18-822	C\$140.39 Volume Pricing	2 In Stock
-	12.50	Hoya UV36N	360.00	1.00	#18-823	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya UV36N	360.00	2.50	#18-824	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya UV36N	360.00	1.00	#18-825	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya UV36N	360.00	2.50	#18-826	C\$70.20 Volume Pricing	16 In Stock
-	50.00	Hoya UV36N	360.00	1.00	#18-827	C\$140.39 Volume Pricing	Contact Us
-	50.00	Hoya UV36N	360.00	2.50	#18-828	C\$140.39 Volume Pricing	1 In Stock
50.8 x 50.8	-	Hoya UV36N	360.00	1.00	#18-829	C\$140.39 Volume Pricing	4 In Stock

50.8 x 50.8	-	Hoya UV36N	360.00	2.50	#18-830	C\$140.39 Volume Pricing	7 In Stock
-	12.50	Hoya L37	370.00	2.50	#66-038	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya L37	370.00	2.50	#66-049	C\$70.20 Volume Pricing	6 In Stock
50.8 x 50.8	-	Hoya L37	370.00	2.50	#66-060	C\$140.39 Volume Pricing	14 In Stock
-	50.00	Hoya L37	370.00	2.50	#66-075	C\$140.39 Volume Pricing	8 In Stock

[#66-076 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

-	12.50	Hoya L38	380.00	1.00	#18-831	C\$50.36 Volume Pricing	12 In Stock
-	12.50	Hoya L38	380.00	2.50	#18-832	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya L38	380.00	1.00	#18-833	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya L38	380.00	2.50	#18-834	C\$70.20 Volume Pricing	13 In Stock
-	50.00	Hoya L38	380.00	1.00	#18-835	C\$140.39 Volume Pricing	10 In Stock
-	50.00	Hoya L38	380.00	2.50	#18-836	C\$140.39 Volume Pricing	1 In Stock
50.8 x 50.8	-	Hoya L38	380.00	1.00	#18-837	C\$140.39 Volume Pricing	8 In Stock
50.8 x 50.8	-	Hoya L38	380.00	2.50	#18-838	C\$140.39 Volume Pricing	7 In Stock
-	12.50	Hoya L39	390.00	1.00	#18-839	C\$50.36 Volume Pricing	20+ In Stock

-	12.50	Hoya L39	390.00	2.50	#18-840	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya L39	390.00	1.00	#18-841	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya L39	390.00	2.50	#18-842	C\$70.20 Volume Pricing	20+ In Stock
-	50.00	Hoya L39	390.00	1.00	#18-843	C\$140.39 Volume Pricing	5 In Stock
-	50.00	Hoya L39	390.00	2.50	#18-844	C\$140.39 Volume Pricing	9 In Stock
50.8 x 50.8	-	Hoya L39	390.00	1.00	#18-845	C\$140.39 Volume Pricing	11 In Stock
50.8 x 50.8	-	Hoya L39	390.00	2.50	#18-846	C\$140.39 Volume Pricing	2 In Stock
-	12.50	Hoya L42	420.00	1.00	#18-847	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya L42	420.00	2.50	#18-848	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya L42	420.00	1.00	#18-849	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya L42	420.00	2.50	#18-850	C\$70.20 Volume Pricing	9 In Stock
-	50.00	Hoya L42	420.00	1.00	#18-851	C\$140.39 Volume Pricing	6 In Stock
-	50.00	Hoya L42	420.00	2.50	#18-852	C\$140.39 Volume Pricing	8 In Stock
50.8 x 50.8	-	Hoya L42	420.00	1.00	#18-853	C\$140.39 Volume Pricing	2 In Stock
50.8 x 50.8	-	Hoya L42	420.00	2.50	#18-854	C\$140.39 Volume Pricing	Contact Us
-	12.50	Hoya Y44	440.00	1.00	#18-855	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya Y44	440.00	2.50	#18-856	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya Y44	440.00	1.00	#18-857	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya Y44	440.00	2.50	#18-858	C\$70.20 Volume Pricing	15 In Stock
-	50.00	Hoya Y44	440.00	1.00	#18-859	C\$140.39 Volume Pricing	7 In Stock
-	50.00	Hoya Y44	440.00	2.50	#18-860	C\$140.39 Volume Pricing	9 In Stock
50.8 x 50.8	-	Hoya Y44	440.00	1.00	#18-861	C\$140.39 Volume Pricing	5 In Stock

50.8 x 50.8	-	Hoya Y44	440.00	2.50	#18-862	C\$140.39 Volume Pricing	1 In Stock
-	12.50	Hoya Y48	480.00	1.00	#18-863	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya Y48	480.00	2.50	#18-864	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya Y48	480.00	1.00	#18-865	C\$70.20 Volume Pricing	8 In Stock
-	25.40	Hoya Y48	480.00	2.50	#18-866	C\$70.20 Volume Pricing	Contact Us
-	50.00	Hoya Y48	480.00	1.00	#18-867	C\$140.39 Volume Pricing	5 In Stock
-	50.00	Hoya Y48	480.00	2.50	#18-868	C\$140.39 Volume Pricing	8 In Stock
50.8 x 50.8	-	Hoya Y48	480.00	1.00	#18-869	C\$140.39 Volume Pricing	1 In Stock
50.8 x 50.8	-	Hoya Y48	480.00	2.50	#18-870	C\$140.39 Volume Pricing	2 In Stock
-	12.50	Hoya Y50	500.00	2.50	#66-039	C\$50.36 Volume Pricing	4 In Stock
-	25.40	Hoya Y50	500.00	2.50	#66-050	C\$70.20 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya Y50	500.00	2.50	#66-061	C\$140.39 Volume Pricing	20+ In Stock
-	50.00	Hoya Y50	500.00	2.50	#66-084	C\$140.39 Volume Pricing	15 In Stock
-	12.50	Hoya Y52	520.00	1.00	#18-871	C\$50.36 Volume Pricing	9 In Stock
-	12.50	Hoya Y52	520.00	2.50	#18-872	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya Y52	520.00	1.00	#18-873	C\$70.20 Volume Pricing	5 In Stock
-	25.40	Hoya Y52	520.00	2.50	#18-874	C\$70.20 Volume Pricing	3 In Stock
-	50.00	Hoya Y52	520.00	1.00	#18-875	C\$140.39 Volume Pricing	7 In Stock
-	50.00	Hoya Y52	520.00	2.50	#18-876	C\$140.39 Volume Pricing	2 In Stock
50.8 x 50.8	-	Hoya Y52	520.00	1.00	#18-877	C\$140.39 Volume Pricing	4 In Stock
50.8 x 50.8	-	Hoya Y52	520.00	2.50	#18-878	C\$140.39 Volume Pricing	9 In Stock
-	12.50	Hoya O54	540.00	2.50	#66-040	C\$50.36 Volume Pricing	20+ In Stock

-	25.40	Hoya O54	540.00	2.50	#66-051	C\$70.20 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya O54	540.00	2.50	#66-062	C\$140.39 Volume Pricing	20+ In Stock
-	50.00	Hoya O54	540.00	2.50	#66-087	C\$140.39 Volume Pricing	15 In Stock
-	12.50	Hoya O56	560.00	2.50	#66-041	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya O56	560.00	2.50	#66-052	C\$70.20 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya O56	560.00	2.50	#66-063	C\$140.39 Volume Pricing	20+ In Stock
-	50.00	Hoya O56	560.00	2.50	#66-089	C\$140.39 Volume Pricing	20+ In Stock
-	12.50	Hoya O58	580.00	2.50	#66-042	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya O58	580.00	2.50	#66-053	C\$70.20 Volume Pricing	20+ In Stock
-	50.00	Hoya O58	580.00	2.50	#66-091	C\$140.39 Volume Pricing	20+ In Stock
-	12.50	Hoya R60	600.00	2.50	#66-043	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya R60	600.00	2.50	#66-054	C\$70.20 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya R60	600.00	2.50	#66-065	C\$140.39 Volume Pricing	20+ In Stock
-	50.00	Hoya R60	600.00	2.50	#66-093	C\$140.39 Volume Pricing	14 In Stock
-	12.50	Hoya R62	620.00	2.50	#66-044	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya R62	620.00	2.50	#66-055	C\$70.20 Volume Pricing	10 In Stock
50.8 x 50.8	-	Hoya R62	620.00	2.50	#66-066	C\$140.39 Volume Pricing	20+ In Stock
-	50.00	Hoya R62	620.00	2.50	#66-095	C\$140.39 Volume Pricing	20+ In Stock
-	12.50	Hoya R64	640.00	1.00	#18-879	C\$50.36 Volume Pricing	17 In Stock
-	12.50	Hoya R64	640.00	2.50	#18-880	C\$50.36 Volume Pricing	8 In Stock
-	25.40	Hoya R64	640.00	1.00	#18-881	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya R64	640.00	2.50	#18-882	C\$70.20 Volume Pricing	20+ In Stock
-	50.00	Hoya R64	640.00	1.00	#18-883	C\$140.39 Volume Pricing	7 In Stock

-	50.00	Hoya R64	640.00	2.50	#18-884	C\$140.39 Volume Pricing	11 In Stock
50.8 x 50.8	-	Hoya R64	640.00	1.00	#18-885	C\$140.39 Volume Pricing	9 In Stock
50.8 x 50.8	-	Hoya R64	640.00	2.50	#18-886	C\$140.39 Volume Pricing	5 In Stock
-	12.50	Hoya R66	660.00	2.50	#66-045	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya R66	660.00	2.50	#66-056	C\$70.20 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya R66	660.00	2.50	#66-067	C\$140.39 Volume Pricing	3 In Stock
-	50.00	Hoya R66	660.00	2.50	#66-098	C\$140.39 Volume Pricing	10 In Stock
-	12.50	Hoya R70	700.00	1.00	#18-887	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya R70	700.00	2.50	#18-888	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya R70	700.00	1.00	#18-889	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya R70	700.00	2.50	#18-890	C\$70.20 Volume Pricing	14 In Stock
-	50.00	Hoya R70	700.00	1.00	#18-891	C\$140.39 Volume Pricing	4 In Stock
-	50.00	Hoya R70	700.00	2.50	#18-892	C\$140.39 Volume Pricing	5 In Stock
50.8 x 50.8	-	Hoya R70	700.00	1.00	#18-893	C\$140.39 Volume Pricing	5 In Stock
50.8 x 50.8	-	Hoya R70	700.00	2.50	#18-894	C\$140.39 Volume Pricing	7 In Stock
-	12.50	Hoya R72	720.00	2.50	#66-046	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya R72	720.00	2.50	#66-057	C\$70.20 Volume Pricing	11 In Stock
50.8 x 50.8	-	Hoya R72	720.00	2.50	#66-068	C\$140.39 Volume Pricing	20+ In Stock
-	50.00	Hoya R72	720.00	2.50	#66-102	C\$140.39 Volume Pricing	13 In Stock
-	12.50	Hoya IR76N	760.00	2.50	#66-047	C\$50.36 Volume Pricing	3 In Stock
-	25.40	Hoya IR76N	760.00	2.50	#66-058	C\$70.20 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya IR76N	760.00	2.50	#66-069	C\$140.39 Volume Pricing	20+ In Stock
-	50.00	Hoya IR76N	760.00	2.50	#66-103	C\$140.39 Volume Pricing	14 In Stock

-	12.50	Hoya IR80N	800.00	2.50	#66-048	C\$50.36 Volume Pricing	17 In Stock
-	25.40	Hoya IR80N	800.00	2.50	#66-059	C\$70.20 Volume Pricing	20+ In Stock
50.8 x 50.8	-	Hoya IR80N	800.00	2.50	#66-070	C\$140.39 Volume Pricing	20+ In Stock
-	50.00	Hoya IR80N	800.00	2.50	#66-105	C\$140.39 Volume Pricing	20+ In Stock
-	12.50	Hoya IR83N	830.00	1.00	#18-895	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya IR83N	830.00	2.50	#18-896	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya IR83N	830.00	1.00	#18-897	C\$70.20 Volume Pricing	14 In Stock
-	25.40	Hoya IR83N	830.00	2.50	#18-898	C\$70.20 Volume Pricing	5 In Stock
-	50.00	Hoya IR83N	830.00	1.00	#18-899	C\$140.39 Volume Pricing	6 In Stock
-	50.00	Hoya IR83N	830.00	2.50	#18-900	C\$140.39 Volume Pricing	1 In Stock
50.8 x 50.8	-	Hoya IR83N	830.00	1.00	#18-901	C\$140.39 Volume Pricing	4 In Stock
50.8 x 50.8	-	Hoya IR83N	830.00	2.50	#18-902	C\$140.39 Volume Pricing	8 In Stock
-	12.50	Hoya IR85N	850.00	1.00	#18-903	C\$50.36 Volume Pricing	13 In Stock
-	12.50	Hoya IR85N	850.00	2.50	#18-904	C\$50.36 Volume Pricing	20+ In Stock
-	25.40	Hoya IR85N	850.00	1.00	#18-905	C\$70.20 Volume Pricing	14 In Stock
-	25.40	Hoya IR85N	850.00	2.50	#18-906	C\$70.20 Volume Pricing	12 In Stock
-	50.00	Hoya IR85N	850.00	1.00	#18-907	C\$140.39 Volume Pricing	2 In Stock
-	50.00	Hoya IR85N	850.00	2.50	#18-908	C\$140.39 Volume Pricing	7 In Stock
50.8 x 50.8	-	Hoya IR85N	850.00	1.00	#18-909	C\$140.39 Volume Pricing	7 In Stock
50.8 x 50.8	-	Hoya IR85N	850.00	2.50	#18-910	C\$140.39 Volume Pricing	4 In Stock
-	12.50	Hoya RM100	1,000.00	1.00	#18-911	C\$50.36 Volume Pricing	20+ In Stock
-	12.50	Hoya RM100	1,000.00	2.50	#18-912	C\$50.36 Volume Pricing	20+ In Stock

-	25.40	Hoya RM100	1,000.00	1.00	#18-913	C\$70.20 Volume Pricing	20+ In Stock
-	25.40	Hoya RM100	1,000.00	2.50	#18-914	C\$70.20 Volume Pricing	20+ In Stock
-	50.00	Hoya RM100	1,000.00	1.00	#18-915	C\$140.39 Volume Pricing	8 In Stock
-	50.00	Hoya RM100	1,000.00	2.50	#18-916	C\$140.39 Volume Pricing	2 In Stock
50.8 x 50.8	-	Hoya RM100	1,000.00	1.00	#18-917	C\$140.39 Volume Pricing	5 In Stock
 Edmund optics worldwide	0.00			2.50	#18-918	C\$140.39 Volume Pricing	1 In Stock

Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA
Phone: 1-800-363-1992 :
www.edmundoptics.com