


[All Products](#) / [Optics](#) / [Optical Filters](#) / [Color and Absorptive Filters](#)

Hoya Colored Glass Bandpass Filters See More by [Hoya](#)



- UV, VIS, IR Ranges
- Circular and Square Sizes Available




Common Specifications

Optical Properties

Substrate: Colored Glass

Coating: Uncoated

Technical Information



Products

CWL (nm)	Glass/Filter Number	Dia. (mm)	Dimensions (mm)	Thickness (mm)	Stock Number	Price	Buy
370.00	Hoya B370	12.00	-	2.50	#48-630	C\$59.85 Volume Pricing	17 In Stock
370.00	Hoya B370	25.40	-	2.50	#48-634	C\$103.60 Volume Pricing	Contact Us
370.00	Hoya B370	-	50.8 x 50.8	2.50	#48-639	C\$176.40 Volume Pricing	20+ In Stock
370.00	Hoya B370	12.00	-	1.00	#18-776	C\$59.85 Volume Pricing	10 In Stock
370.00	Hoya B370	25.40	-	1.00	#18-777	C\$103.60 Volume Pricing	20+ In Stock
370.00	Hoya B370	50.00	-	1.00	#18-778	C\$176.40 Volume Pricing	2 In Stock
370.00	Hoya B370	50.00	-	2.50	#18-779	C\$176.40 Volume Pricing	2 In Stock
370.00	Hoya B370	-	50.80 x 50.80	1.00	#18-780	C\$176.40 Volume Pricing	4 In Stock
390.00	Hoya B390	12.00	-	2.50	#48-631	C\$59.85 Volume Pricing	9 In Stock
390.00	Hoya B390	25.40	-	2.50	#48-635	C\$103.60 Volume Pricing	14 In Stock
390.00	Hoya B390	-	50.8 x 50.8	2.50	#48-640	C\$176.40 Volume Pricing	20+ In Stock
390.00	Hoya B390	12.00	-	1.00	#18-781	C\$59.85 Volume Pricing	20+ In Stock
390.00	Hoya B390	25.40	-	1.00	#18-782	C\$103.60 Volume Pricing	20+ In Stock
390.00	Hoya B390	50.00	-	1.00	#18-783	C\$176.40 Volume Pricing	5 In Stock
390.00	Hoya B390	50.00	-	2.50	#18-784	C\$176.40 Volume Pricing	4 In Stock
390.00	Hoya B390	-	50.80 x 50.80	1.00	#18-785	C\$176.40 Volume Pricing	5 In Stock
410.00	Hoya B410	12.00	-	2.50	#34-431	C\$59.85 Volume Pricing	8 In Stock

410.00	Hoya B410	-	25.0 x 25.0	2.50	#34-432	C\$103.60 Volume Pricing	5 In Stock
410.00	Hoya B410	25.40	-	2.50	#34-433	C\$103.60 Volume Pricing	8 In Stock
410.00	Hoya B410	-	50.8 x 50.8	2.50	#34-434	C\$176.40 Volume Pricing	4 In Stock
440.00	Hoya B440	12.00	-	2.50	#48-632	C\$59.85 Volume Pricing	20+ In Stock
440.00	Hoya B440	25.40	-	2.50	#48-636	C\$103.60 Volume Pricing	20+ In Stock
440.00	Hoya B440	-	50.8 x 50.8	2.50	#48-641	C\$176.40 Volume Pricing	13 In Stock
460.00	Hoya B460	12.00	-	2.50	#34-443	C\$59.85 Volume Pricing	5 In Stock
460.00	Hoya B460	-	25.0 x 25.0	2.50	#34-444	C\$103.60 Volume Pricing	1 In Stock
460.00	Hoya B460	25.40	-	2.50	#34-445	C\$103.60 Volume Pricing	4 In Stock
460.00	Hoya B460	-	50.8 x 50.8	2.50	#34-446	C\$176.40 Volume Pricing	Contact Us
530.00	Hoya G530	12.00	-	2.50	#34-435	C\$74.20 Volume Pricing	2 In Stock
530.00	Hoya G530	-	25.0 x 25.0	2.50	#34-436	C\$105.00 Volume Pricing	8 In Stock
530.00	Hoya G530	25.40	-	2.50	#34-437	C\$105.00 Volume Pricing	Contact Us
530.00	Hoya G530	-	50.8 x 50.8	2.50	#34-438	C\$176.40 Volume Pricing	16 In Stock
533.00	Hoya G533	12.00	-	2.50	#34-447	C\$74.20 Volume Pricing	9 In Stock
533.00	Hoya G533	-	25.0 x 25.0	2.50	#34-448	C\$105.00 Volume Pricing	7 In Stock
533.00	Hoya G533	25.40	-	2.50	#34-449	C\$105.00 Volume Pricing	6 In Stock
533.00	Hoya G533	-	50.8 x 50.8	2.50	#34-450	C\$179.20 Volume Pricing	6 In Stock
545.00	Hoya G545	12.00	-	2.50	#34-439	C\$74.20 Volume Pricing	6 In Stock
545.00	Hoya G545	-	25.0 x 25.0	2.50	#34-440	C\$105.00 Volume Pricing	5 In Stock

545.00	Hoya G545	25.40	-	2.50	#34-441	C\$105.00 Volume Pricing	7 In Stock
545.00	Hoya G545	-	50.8 x 50.8	2.50	#34-442	C\$179.20 Volume Pricing	6 In Stock
550.00	Hoya G550	12.00	-	2.50	#34-451	C\$74.20 Volume Pricing	5 In Stock
550.00	Hoya G550	-	25.0 x 25.0	2.50	#34-452	C\$105.00 Volume Pricing	6 In Stock
550.00	Hoya G550	25.40	-	2.50	#34-453	C\$105.00 Volume Pricing	15 In Stock
550.00	Hoya G550	-	50.8 x 50.8	2.50	#34-454	C\$179.20 Volume Pricing	Contact Us
830.00	Hoya RT830	12.00	-	2.50	#46-082	C\$59.85 Volume Pricing	20+ In Stock
830.00	Hoya RT830	25.40	-	2.50	#46-443	C\$103.60 Volume Pricing	5 In Stock
830.00	Hoya RT830	-	25.0 x 25.0	2.50	#46-086	C\$103.60 Volume Pricing	20+ In Stock
830.00	Hoya RT830	-	50.8 x 50.8	2.50	#46-444	C\$176.40 Volume Pricing	8 In Stock
830.00	Hoya RT830	12.00	-	1.00	#18-786	C\$59.85 Volume Pricing	9 In Stock
830.00	Hoya RT830	25.40	-	1.00	#18-787	C\$103.60 Volume Pricing	20+ In Stock
830.00	Hoya RT830	50.00	-	1.00	#18-788	C\$176.40 Volume Pricing	8 In Stock
830.00	Hoya RT830	50.00	-	2.50	#18-789	C\$176.40 Volume Pricing	4 In Stock
830.00	Hoya RT830	-	50.80 x 50.80	1.00	#18-790	C\$176.40 Volume Pricing	4 In Stock
330.00	Hoya U330	12.00	-	2.50	#46-095	C\$67.55 Volume Pricing	20+ In Stock
330.00	Hoya U330	25.40	-	2.50	#46-437	C\$128.80 Volume Pricing	20+ In Stock
330.00	Hoya U330	-	25.0 x 25.0	2.50	#46-083	C\$128.80 Volume Pricing	15 In Stock
330.00	Hoya U330	-	50.8 x 50.8	2.50	#46-438	C\$277.20 Volume Pricing	12 In Stock
330.00	Hoya U330	12.00	-	1.00	#18-761	C\$67.55 Volume Pricing	20+ In Stock

330.00	Hoya U330	25.40	-	1.00	#18-762	C\$128.80 Volume Pricing	14 In Stock
330.00	Hoya U330	50.00	-	1.00	#18-763	C\$277.20 Volume Pricing	5 In Stock
330.00	Hoya U330	50.00	-	2.50	#18-764	C\$277.20 Volume Pricing	9 In Stock
330.00	Hoya U330	-	50.80 x 50.80	1.00	#18-765	C\$277.20 Volume Pricing	7 In Stock
340.00	Hoya U340	12.00	-	2.50	#46-096	C\$67.55 Volume Pricing	20+ In Stock
340.00	Hoya U340	25.40	-	2.50	#46-439	C\$128.80 Volume Pricing	20+ In Stock
340.00	Hoya U340	-	25.0 x 25.0	2.50	#46-084	C\$128.80 Volume Pricing	4 In Stock
340.00	Hoya U340	-	50.8 x 50.8	2.50	#46-440	C\$277.20 Volume Pricing	10 In Stock
340.00	Hoya U340	12.00	-	1.00	#18-766	C\$67.55 Volume Pricing	20+ In Stock
340.00	Hoya U340	25.40	-	1.00	#18-767	C\$128.80 Volume Pricing	6 In Stock
340.00	Hoya U340	50.00	-	1.00	#18-768	C\$277.20 Volume Pricing	3 In Stock
340.00	Hoya U340	50.00	-	2.50	#18-769	C\$277.20 Volume Pricing	4 In Stock
340.00	Hoya U340	-	50.80 x 50.80	1.00	#18-770	C\$277.20 Volume Pricing	5 In Stock
360.00	Hoya U360	12.00	-	2.50	#46-081	C\$67.55 Volume Pricing	20+ In Stock
360.00	Hoya U360	25.40	-	2.50	#46-441	C\$128.80 Volume Pricing	14 In Stock
360.00	Hoya U360	-	25.0 x 25.0	2.50	#46-085	C\$128.80 Volume Pricing	20+ In Stock
360.00	Hoya U360	-	50.8 x 50.8	2.50	#46-442	C\$277.20 Volume Pricing	10 In Stock
360.00	Hoya U360	12.00	-	1.00	#18-771	C\$67.55 Volume Pricing	20+ In Stock
360.00	Hoya U360	25.40	-	1.00	#18-772	C\$128.80 Volume Pricing	20+ In Stock
360.00	Hoya U360	50.00	-	1.00	#18-773	C\$277.20 Volume Pricing	8 In Stock

360.00	Hoya U360	50.00	-	2.50	#18-774	C\$277.20 Volume Pricing	7 In Stock
	Edmund optics worldwide	1.00			#18-775	C\$277.20 Volume Pricing	4 In Stock

Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA
 Phone: 1-800-363-1992 :
www.edmundoptics.com