

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Achromatic Lenses](#)

TECHSPEC® Broadband AR Coated Negative Achromatic Lenses



- VIS 0° and VIS-NIR Coatings
- 6.25 – 25mm Diameter Options
- [MgF₂ Coated Negative Achromatic Lenses](#) also Available

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed
--------	----------------------

Optical Properties

Focal Length Tolerance (%)	±1
----------------------------	----


Focal Length Specification Wavelength (nm):	587.6
---	-------

Surface Quality:	40-20
------------------	-------

Power (P-V) @ 632.8nm:	1.5λ
------------------------	------

Irregularity (P-V) @ 632.8nm:	λ/4
-------------------------------	-----

Technical Information



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Substrate	Coating	Stock Number	Price	Buy
6.25	-10.00	-11.92	N-BAF10 / N-SF10	VIS 0° (425-675nm)	#62-478	C\$112.64 Volume Pricing	20+ In Stock
6.25	-10.00	-11.92	N-BAF10 / N-SF10	VIS-NIR (400-1000nm)	#85-877	C\$121.72 Volume Pricing	20+ In Stock
#62-480 Clearance							
 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
6.25	-25.00	-26.53	N-BAF10 / N-SF10	VIS 0° (425-675nm)		C\$48.31	20+ In Stock
12.50	-15.00	-18.08	N-BAF10 / N-SF10	VIS 0° (425-675nm)	#62-484	C\$136.08 Volume Pricing	20+ In Stock
12.50	-20.00	-22.88	N-BAF10 / N-SF10	VIS 0° (425-675nm)	#62-485	C\$136.08 Volume Pricing	20+ In Stock
12.50	-25.00	-27.33	N-BAF10 / N-SF10	VIS 0° (425-675nm)	#62-486	C\$136.08 Volume Pricing	20+ In Stock
12.50	-35.00	-36.51	N-BK7 / N-SF5	VIS 0° (425-675nm)	#62-487	C\$136.08 Volume Pricing	20+ In Stock

12.50	-50.00	-51.58	N-BK7 / N-SF5	VIS 0° (425-675nm)	#62-488	C\$136.08 Volume Pricing	20+ In Stock
12.50	-75.00	-77.47	N-BK7 / N-SF5	VIS 0° (425-675nm)	#62-489	C\$136.08 Volume Pricing	11 In Stock
25.00	-50.00	-53.33	N-BAF10 / N-SF10	VIS 0° (425-675nm)	#62-492	C\$178.42 Volume Pricing	Contact Us
25.00	-75.00	-77.65	N-BK7 / N-SF5	VIS 0° (425-675nm)	#62-493	C\$178.42 Volume Pricing	20+ In Stock
25.00	-	-	N-BAF10 / N-SF10	VIS 0° (425-675nm)	#62-494	C\$178.42 Volume Pricing	20+ In Stock
25.00	-	-	N-BK7 / N-SF5	VIS 0° (425-675nm)	#62-495	C\$178.42 Volume Pricing	20+ In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA
 Phone: 1-800-363-1992 :
www.edmundoptics.com