

[All Products](#) / [Optomechanics](#) / [Optical Cage System](#) / [Cage System Optical Mounts](#)

TECHSPEC® M23.2 and M27.5 Fixed Tubes and Retaining Rings



- Fit within Inner Diameter of [Cage System Plates](#)
- Use with Retaining Ring Pairs to Secure Optics
- Join Multiple with Adjustable Length Tubes and Thread Adapters

Common Specifications

General

Function:	Fixed
-----------	-------

Physical & Mechanical Properties

Construction:	Black Anodized Aluminum
---------------	-------------------------

Technical Information

Products

Note	Compatible Plate Inner Diameter (mm)	Length (mm)	Size of Compatible Optics (mm)	Thread Type	Outer Diameter (mm)	Stock Number	Price	Buy
Fixed Tube	25.0	5.00	-	M23.2 x 0.75	25.0	#85-517	C\$43.40	20+ In Stock
Fixed Tube	25.0	10.00	-	M23.2 x 0.75	25.0	#85-518	C\$43.40	20+ In Stock
Fixed Tube	25.0	15.00	-	M23.2 x 0.75	25.0	#85-519	C\$51.45	20+ In Stock
Fixed Tube	25.0	20.00	-	M23.2 x 0.75	25.0	#85-520	C\$51.45	10 In Stock
Fixed Tube	25.0	25.00	-	M23.2 x 0.75	25.0	#85-521	C\$51.45	20+ In Stock
Fixed Tube	25.0	30.00	-	M23.2 x 0.75	25.0	#85-522	C\$62.30	16 In Stock
Fixed Tube	25.0	50.00	-	M23.2 x 0.75	25.0	#85-523	C\$70.00	5 In Stock
Fixed Tube	30.0	5.00	-	M27.5 x 0.75	30.0	#85-586	C\$43.40	20+ In Stock
Fixed Tube	30.0	10.00	-	M27.5 x 0.75	30.0	#85-589	C\$43.40	20+ In Stock
Fixed Tube	30.0	15.00	-	M27.5 x 0.75	30.0	#85-590	C\$51.45	6 In Stock
Fixed Tube	30.0	20.00	-	M27.5 x 0.75	30.0	#85-593	C\$51.45	6 In Stock
Fixed Tube	30.0	25.00	-	M27.5 x 0.75	30.0	#85-594	C\$51.45	20+ In Stock
Fixed Tube	30.0	50.00	-	M27.5 x 0.75	30.0	#85-600	C\$70.00	20+ In Stock
Retaining Ring	-	3.00	6.0	M23.2 x 0.75	-	#85-566	C\$51.45	1 In Stock
Retaining Ring	-	3.00	6.5	M23.2 x 0.75	-	#85-565	C\$51.45	11 In Stock
Retaining Ring	-	3.00	9.0	M23.2 x 0.75	-	#85-564	C\$51.45	2 In Stock
Retaining Ring	-	3.00	10.0	M23.2 x 0.75	-	#85-563	C\$51.45	3 In Stock

Retaining Ring	-	3.00	12.0	M23.2 x 0.75	-	#85-562	C\$51.45	2 In Stock
Retaining Ring	-	3.00	12.5	M23.2 x 0.75	-	#85-561	C\$51.45	2 In Stock
Retaining Ring	-	3.00	12.7	M23.2 x 0.75	-	#85-560	C\$51.45	1 In Stock
Retaining Ring	-	3.00	15.0	M23.2 x 0.75	-	#85-559	C\$51.45	1 In Stock
Retaining Ring	-	3.00	18.0	M23.2 x 0.75	-	#85-558	C\$51.45	Contact Us
Retaining Ring	-	3.00	20.0	M23.2 x 0.75	-	#85-556	C\$51.45	20+ In Stock
Retaining Ring	-	3.00	25.0	M27.5 x 0.75	-	#85-597	C\$51.45	13 In Stock
Retaining Ring	-	3.00	25.4	M27.5 x 0.75	-	#85-596	C\$51.45	Contact Us



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com