


[All Products](#) /
 [Optics](#) /
 [Optical Lenses](#) /
 [Cylinder Lenses](#) /
 [Imaging Grade Cylinder Lenses](#)

TECHSPEC® Imaging Grade PCX Cylinder Lenses



- Ideal for Beam Shaping Applications
- Tightly Controlled Optical and Geometric Tolerances
- Rectangular and Circular Form Factors Available

Common Specifications

Physical & Mechanical Properties

Bevel: Protective as needed	Center Thickness Tolerance (mm): ±0.1
Optical Properties	
Substrate: N-BK7	Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ	Irregularity (P-V) @ 632.8nm: λ/4

Technical Information

Products

Dia. (mm)	Dimensions (mm)	EFL (mm)	Substrate	Coating	Stock Number	Price	Buy
12.70	-	50.00	N-BK7	Uncoated	#34-606	C\$144.11 Volume Pricing	20+ In Stock
12.70	-	75.00	N-BK7	Uncoated	#34-607	C\$144.11 Volume Pricing	20+ In Stock
12.70	-	100.00	N-BK7	Uncoated	#34-608	C\$144.11 Volume Pricing	20+ In Stock
12.70	-	50.00	N-BK7	VIS 0° (425-675nm)	#34-648	C\$163.27 Volume Pricing	3 In Stock
12.70	-	75.00	N-BK7	VIS 0° (425-675nm)	#34-649	C\$163.27 Volume Pricing	2 In Stock
12.70	-	100.00	N-BK7	VIS 0° (425-675nm)	#34-650	C\$163.27 Volume Pricing	Contact Us
12.70	-	50.00	N-BK7	NIR I (600-1050nm)	#34-668	C\$163.27 Volume Pricing	Contact Us
12.70	-	75.00	N-BK7	NIR I (600-1050nm)	#34-669	C\$163.27 Volume Pricing	1 In Stock
12.70	-	100.00	N-BK7	NIR I (600-1050nm)	#34-670	C\$163.27 Volume Pricing	5 In Stock
12.70	-	50.00	N-BK7	NIR II (750-1550nm)	#34-627	C\$163.27 Volume Pricing	Contact Us
12.70	-	75.00	N-BK7	NIR II (750-1550nm)	#34-628	C\$163.27 Volume Pricing	5 In Stock
12.70	-	100.00	N-BK7	NIR II (750-1550nm)	#34-629	C\$163.27 Volume Pricing	5 In Stock
25.40	-	50.00	N-BK7	Uncoated	#34-611	C\$152.44 Volume Pricing	20+ In Stock
25.40	-	75.00	N-BK7	Uncoated	#34-612	C\$152.44 Volume Pricing	20+ In Stock

25.40	-	100.00	N-BK7	Uncoated	#34-613	C\$152.44 Volume Pricing	7 In Stock
25.40	-	150.00	N-BK7	Uncoated	#34-614	C\$152.44 Volume Pricing	Contact Us
25.40	-	50.00	N-BK7	NIR II (750-1550nm)	#34-631	C\$181.59 Volume Pricing	8 In Stock
25.40	-	75.00	N-BK7	NIR II (750-1550nm)	#34-632	C\$181.59 Volume Pricing	5 In Stock
25.40	-	100.00	N-BK7	NIR II (750-1550nm)	#34-633	C\$181.59 Volume Pricing	3 In Stock
25.40	-	150.00	N-BK7	NIR II (750-1550nm)	#34-634	C\$181.59 Volume Pricing	12 In Stock
25.40	-	50.00	N-BK7	VIS 0° (425-675nm)	#34-652	C\$181.59 Volume Pricing	4 In Stock
25.40	-	75.00	N-BK7	VIS 0° (425-675nm)	#34-653	C\$181.59 Volume Pricing	9 In Stock
25.40	-	100.00	N-BK7	VIS 0° (425-675nm)	#34-654	C\$181.59 Volume Pricing	3 In Stock
25.40	-	150.00	N-BK7	VIS 0° (425-675nm)	#34-655	C\$181.59 Volume Pricing	10 In Stock
25.40	-	50.00	N-BK7	NIR I (600-1050nm)	#34-672	C\$181.59 Volume Pricing	2 In Stock
25.40	-	75.00	N-BK7	NIR I (600-1050nm)	#34-673	C\$181.59 Volume Pricing	9 In Stock
25.40	-	100.00	N-BK7	NIR I (600-1050nm)	#34-674	C\$181.59 Volume Pricing	11 In Stock
25.40	-	150.00	N-BK7	NIR I (600-1050nm)	#34-675	C\$181.59 Volume Pricing	2 In Stock
-	12.7 x 12.7	50.00	N-BK7	Uncoated	#34-752	C\$152.44 Volume Pricing	20+ In Stock

-	12.7 x 12.7	50.00	N-BK7	VIS 0° (425-675nm)	#34-986	C\$181.59 Volume Pricing	3 In Stock
-	12.7 x 12.7	50.00	N-BK7	NIR I (600-1050nm)	#34-998	C\$171.60 Volume Pricing	1 In Stock
-	12.7 x 12.7	50.00	N-BK7	NIR II (750-1550nm)	#35-010	C\$181.59 Volume Pricing	15 In Stock
-	25.4 x 25.4	25.00	N-BK7	Uncoated	#34-753	C\$171.60 Volume Pricing	20+ In Stock
-	25.4 x 25.4	50.00	N-BK7	Uncoated	#34-754	C\$163.27 Volume Pricing	17 In Stock
-	25.4 x 25.4	75.00	N-BK7	Uncoated	#34-755	C\$163.27 Volume Pricing	20+ In Stock
-	25.4 x 25.4	25.00	N-BK7	VIS 0° (425-675nm)	#34-987	C\$198.25 Volume Pricing	3 In Stock
-	25.4 x 25.4	50.00	N-BK7	VIS 0° (425-675nm)	#34-988	C\$181.59 Volume Pricing	15 In Stock
-	25.4 x 25.4	75.00	N-BK7	VIS 0° (425-675nm)	#34-989	C\$189.92 Volume Pricing	5 In Stock
-	25.4 x 25.4	25.00	N-BK7	NIR I (600-1050nm)	#34-999	C\$198.25 Volume Pricing	8 In Stock
-	25.4 x 25.4	50.00	N-BK7	NIR I (600-1050nm)	#35-000	C\$189.92 Volume Pricing	16 In Stock
-	25.4 x 25.4	75.00	N-BK7	NIR I (600-1050nm)	#35-001	C\$189.92 Volume Pricing	20+ In Stock
-	25.4 x 25.4	25.00	N-BK7	NIR II (750-1550nm)	#35-011	C\$198.25 Volume Pricing	13 In Stock
-	25.4 x 25.4	50.00	N-BK7	NIR II (750-1550nm)	#35-012	C\$189.92 Volume Pricing	10 In Stock
-	25.4 x 25.4	75.00	N-BK7	NIR II (750-1550nm)	#35-013	C\$189.92 Volume Pricing	1 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com