

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Pinholes and Slits](#)

Acktar Blackened Pinholes See More by [Acktar](#)



- Low Reflectance from the EUV to SWIR
- 99% Absorbance Blackening Coating
- Aperture Sizes from 20 to 1000µm
- Available Unmounted and Mounted

Common Specifications

Physical & Mechanical Properties

Construction:	Stainless Steel
----------------------	-----------------

Material Properties

Absorbance (%):	99
------------------------	----

Technical Information

Products

Type	Outer Diameter (mm)	Construction	Fixed Aperture Diameter (μm)	Stock Number	Price	Buy
Unmounted	9.53	Stainless Steel	20	#15-386	C\$246.75 Volume Pricing	3 In Stock
Unmounted	9.53	Stainless Steel	25	#15-387	C\$246.75 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	50	#12-166	C\$246.75 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	75	#15-388	C\$246.75 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	100	#12-167	C\$246.75 Volume Pricing	5 In Stock
Unmounted	9.53	Stainless Steel	150	#15-389	C\$246.75 Volume Pricing	4 In Stock
Unmounted	9.53	Stainless Steel	200	#12-168	C\$246.75 Volume Pricing	5 In Stock
Unmounted	9.53	Stainless Steel	300	#15-390	C\$246.75 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	400	#15-391	C\$246.75 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	500	#12-169	C\$246.75 Volume Pricing	4 In Stock
Unmounted	9.53	Stainless Steel	600	#15-392	C\$246.75 Volume Pricing	8 In Stock
Unmounted	9.53	Stainless Steel	800	#16-738	C\$246.75 Volume Pricing	4 In Stock
Unmounted	9.53	Stainless Steel	1000	#12-170	C\$246.75 Volume Pricing	5 In Stock
Mounted	12.7	Stainless Steel	25	#16-821	C\$264.25 Volume Pricing	3 In Stock
Mounted	12.7	Stainless Steel	50	#16-822	C\$264.25 Volume Pricing	20+ In Stock
Mounted	12.7	Stainless Steel	75	#16-823	C\$264.25 Volume Pricing	20+ In Stock
Mounted	12.7	Stainless Steel	100	#16-824	C\$264.25 Volume Pricing	2 In Stock

Mounted	12.7	Stainless Steel	150	#16-825	C\$264.25 Volume Pricing	1 In Stock
Mounted	12.7	Stainless Steel	200	#16-826	C\$264.25 Volume Pricing	2 In Stock
Mounted	12.7	Stainless Steel	300	#16-827	C\$264.25 Volume Pricing	4 In Stock
Mounted	12.7	Stainless Steel	500	#16-828	C\$264.25 Volume Pricing	5 In Stock
Mounted	12.7	Stainless Steel	1000	#16-829	C\$264.25 Volume Pricing	Contact Us
Mounted	25.0	Stainless Steel	20	#15-393	C\$264.25 Volume Pricing	4 In Stock
Mounted	25.0	Stainless Steel	25	#15-394	C\$264.25 Volume Pricing	5 In Stock
Mounted	25.0	Stainless Steel	50	#12-171	C\$264.25 Volume Pricing	5 In Stock
Mounted	25.0	Stainless Steel	75	#15-395	C\$264.25 Volume Pricing	3 In Stock
Mounted	25.0	Stainless Steel	100	#12-172	C\$264.25 Volume Pricing	6 In Stock
Mounted	25.0	Stainless Steel	150	#15-396	C\$264.25 Volume Pricing	4 In Stock
Mounted	25.0	Stainless Steel	200	#12-173	C\$264.25 Volume Pricing	5 In Stock
Mounted	25.0	Stainless Steel	300	#15-397	C\$264.25 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	400	#15-398	C\$264.25 Volume Pricing	3 In Stock
Mounted	25.0	Stainless Steel	500	#12-174	C\$264.25 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	600	#15-399	C\$264.25 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	800	#16-739	C\$264.25 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	1000	#12-175	C\$264.25 Volume Pricing	1 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com