


[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#) / [Absorptive \(Dichroic\) Polarizers](#) / [Laminated Film Polarizers](#)

TECHSPEC®

High Contrast Glass Linear Polarizers (XP42)



- Uncoated and Visible AR Coated Options
- >99.98% Polarization Efficiency
- 42% Transmission for Uncoated and 45% Transmission for AR Coated Versions
- XP42 [Plastic](#) and [Film](#) Also Available

Common Specifications

Physical & Mechanical Properties				
Thickness (mm):		2.00 ±0.10	Dimensional Tolerance (mm):	+0.00/-0.20
Construction:		Laminated Glass Polarizing Film		
Optical Properties				
Extinction Ratio:		9000:1 @ 546nm		
Substrate:		XP42 Laminated Between Glass		
		Polarization Efficiency (%):		>99.98 @ 546nm
Environmental & Durability Factors				
Operating Temperature (°C):		-10 to +55		

Technical Information

Products

Extinction Ratio	Wavelength Range (nm)	Dia. (mm)	Dimensional Tolerance (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
9000:1	400 - 700	12.50	+0.00/-0.20	2.00	Uncoated	#19-641	C\$177.80 Volume Pricing	20+ In Stock
9000:1	400 - 700	15.00	+0.00/-0.20	2.00	Uncoated	#19-642	C\$194.60 Volume Pricing	14 In Stock
9000:1	400 - 700	20.00	+0.00/-0.20	2.00	Uncoated	#19-643	C\$210.00 Volume Pricing	9 In Stock
9000:1	400 - 700	25.00	+0.00/-0.20	2.00	Uncoated	#19-644	C\$218.40 Volume Pricing	4 In Stock
9000:1	400 - 700	25.40	+0.00/-0.20	2.00	Uncoated	#19-645	C\$218.40 Volume Pricing	4 In Stock
9000:1	400 - 700	50.00	+0.00/-0.20	2.00	Uncoated	#19-646	C\$267.40 Volume Pricing	20+ In Stock
9000:1	425 - 700	12.50	+0.00/-0.20	2.00	VIS AR Coated	#19-647	C\$194.60 Volume Pricing	13 In Stock
9000:1	425 - 700	15.00	+0.00/-0.20	2.00	VIS AR Coated	#19-648	C\$210.00 Volume Pricing	5 In Stock
9000:1	425 - 700	20.00	+0.00/-0.20	2.00	VIS AR Coated	#19-649	C\$226.80 Volume Pricing	20+ In Stock
9000:1	425 - 700	25.00	+0.00/-0.20	2.00	VIS AR Coated	#19-650	C\$235.20 Volume Pricing	13 In Stock
9000:1	425 - 700	25.40	+0.00/-0.20	2.00	VIS AR Coated	#19-651	C\$235.20 Volume Pricing	6 In Stock
9000:1	425 - 700	50.00	+0.00/-0.20	2.00	VIS AR Coated	#19-652	C\$284.20 Volume Pricing	13 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA
 Phone: 1-800-363-1992 :
www.edmundoptics.com