



[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

Teledyne FLIR IIS Oryx®10GigE Cameras

See More by [Teledyne FLIR](#)



- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



Teledyne  
Authorized  
Distributor

Common Specifications

General			
Manufacturer: FLIR		Camera Series: Oryx®	
Physical & Mechanical Properties			
Housing: Full			
Sensor			
Image Buffer: 240MB			
Type of Sensor: Progressive Scan CMOS		Shutter Type: Global	
Machine Vision Standard: GigE Vision			
Hardware & Interface Connectivity			
Interface: 10GigE			
Connector: GigE interface with Screw Locks		Power Supply: Power Supply Required and Sold Separately: USA: <a href="#">#19-803</a> Europe: <a href="#">#19-803</a> Japan: <a href="#">#19-803</a> Korea: Not Available China: <a href="#">#19-803</a>	
Synchronization: Hardware Trigger (GPIO) or Software Trigger		Interface Port Orientation: Back Panel	
GPIO Connector Type: 12-pin Hirose (HR10)			
Environmental & Durability Factors			
Storage Temperature (°C):		-30 to +60	

**Technical Information**

Products

Type	Model Number	Sensor Format	Resolution (Megapixels)	Connector	Mount	Stock Number	Price	Buy
Monochrome Camera	ORX-10GS-89S6M-C	1"	8.90	GigE interface with Screw Locks	C-Mount	<a href="#">#19-792</a>	C\$7,482.16	1 In Stock



Recertified

Stock No.: 19-792-RCD-05P  
Recertified Code: 05P (All Original  
Parts Included, Perfect)

# Recertified Products

Typically 1-2 Recertified Products are  
in stock at a time. Please contact our  
sales team if you would like exact  
availability of an item.

Recertified products are those  
identified with the recertified logo  
indicating they were returned to  
Edmund Optics® and cannot be sold  
as new for the following reasons:

- Open Box – Missing original  
packaging
- Cosmetic Blemishes –  
Scratches, rub marks or other  
minor cosmetic imperfections
- Service/Repair – Product has  
been serviced to the factory  
original specification
- Factory Returns – Product has  
been returned in its original  
condition

Monochrome      ORX-  
Camera      10GS-  
                 89S6M-  
                 C  
  
1"      8.90      GigE  
                 interface  
                 with Screw  
                 Locks      C-  
                 Mount

Recertified products are inspected for  
damage and any necessary repairs are  
made. Products are then certified by  
Edmund Optics® to be in good working  
order. Since quantity is low, recertified  
products are sold on a first come, first  
serve basis. Any imperfections will be  
listed in the description, indicated in the  
stock number, and categorized by the  
table below. When purchasing  
recertified products, the Edmund  
Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the  
Web Specials section of our website.

C\$7,801.16

1 In Stock

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
	04 Missing Manual	N	Minor Defect/Scratches
	03 Missing Manual and Small Accessory	J	Major Defect/Scratches
	02 Missing Manual and Large Accessory		



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)