


[All Products](#) / [Laser Optics](#) / [Laser Mirrors](#) / [Laser Line Mirrors](#)

TECHSPEC®

Nd:YAG ZERODUR Laser Line Mirrors



- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- >99.5% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Damage Threshold Specifications

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%):	>90	Parallelism (arcsec):	30
---------------------	-----	-----------------------	----

Optical Properties

Substrate:	ZERODUR®	Angle of Incidence (°):	45
Coating Type:	Dielectric	Surface Flatness (P-V):	λ/10
Surface Quality:	20-10		

Technical Information

Products

Title	Stock Number	Price	Buy
10mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror	#26-404	C\$259.70 Volume Pricing	5 In Stock
15mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror	#26-405	C\$274.54 Volume Pricing	5 In Stock
20mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror	#26-406	C\$296.80 Volume Pricing	Contact Us
25mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror	#26-407	C\$311.64 Volume Pricing	4 In Stock
10mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror	#26-414	C\$259.70 Volume Pricing	14 In Stock
15mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror	#26-415	C\$274.54 Volume Pricing	5 In Stock
20mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror	#26-416	C\$296.80 Volume Pricing	9 In Stock
25mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror	#26-417	C\$311.64 Volume Pricing	5 In Stock
10mm Dia. 532nm 45°, Nd:YAG Laser Line Mirror	#26-424	C\$259.70 Volume Pricing	9 In Stock
15mm Dia. 532nm 45°, Nd:YAG Laser Line Mirror	#26-425	C\$274.54 Volume Pricing	9 In Stock
20mm Dia. 532nm 45°, Nd:YAG Laser Line Mirror	#26-426	C\$296.80 Volume Pricing	8 In Stock
25mm Dia. 532nm 45°, Nd:YAG Laser Line Mirror	#26-427	C\$311.64 Volume Pricing	1 In Stock
10mm Dia. 1064nm 45°, Nd:YAG Laser Line Mirror	#26-434	C\$259.70 Volume Pricing	20+ In Stock
15mm Dia. 1064nm 45°, Nd:YAG Laser Line Mirror	#26-435	C\$274.54 Volume Pricing	14 In Stock
20mm Dia. 1064nm 45°, Nd:YAG Laser Line Mirror	#26-436	C\$296.80 Volume Pricing	1 In Stock
25mm Dia. 1064nm 45°, Nd:YAG Laser Line Mirror	#26-437	C\$311.64 Volume Pricing	20+ In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com