

[All Products](#) / [Laser Optics](#) / [Laser Mirrors](#) / [Laser Mirror Substrates](#)
TECHSPEC® Uncoated Convex Laser Mirrors


- High Precision Fused Silica Mirror Substrates
- Large Selection of Diameters and Focal Lengths
- Custom Coating Options Available

Common Specifications

Physical & Mechanical Properties




Back Surface:	Commercial Polish	Clear Aperture (%):	90
Edge Thickness ET (mm):	6.00 ±0.2		

Optical Properties

Coating:	Uncoated		
Effective Focal Length EFL (mm):	6.00	Substrate:	Fused Silica (Corning 7980)
Surface Quality:	20-10		

Technical Information

Products

Title	Stock Number	Price	Buy
#27-600 New			
			
12.7mm Dia. x 50mm ROC, Uncoated, Convex Laser Mirror	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	C\$160.27 Volume Pricing	5 In Stock
#27-601 New			
			
12.7mm Dia. x 100mm ROC, Uncoated, Convex Laser Mirror	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	C\$160.27 Volume Pricing	5 In Stock
#27-602 New			
			
12.7mm Dia. x 150mm ROC, Uncoated, Convex Laser Mirror	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	C\$160.27 Volume Pricing	5 In Stock

[#27-603 New](#)



12.7mm Dia. x
200mm ROC,
Uncoated, Convex
Laser Mirror

New

Launched on our website before
appearing in our latest print
catalogs. Be the first to buy
before anyone else!

C\$160.27
[Volume Pricing](#)

5 In Stock

[#27-604 New](#)



12.7mm Dia. x
300mm ROC,
Uncoated, Convex
Laser Mirror

New

Launched on our website before
appearing in our latest print
catalogs. Be the first to buy
before anyone else!

C\$160.27
[Volume Pricing](#)

5 In Stock

[#27-605 New](#)



12.7mm Dia. x
400mm ROC,
Uncoated, Convex
Laser Mirror

New

Launched on our website before
appearing in our latest print
catalogs. Be the first to buy
before anyone else!

C\$160.27
[Volume Pricing](#)

5 In Stock

12.7mm Dia. x
500mm ROC,
Uncoated, Convex
Laser Mirror

[#27-620](#)

C\$160.27
[Volume Pricing](#)

1 In Stock

25.4mm Dia. x 50mm
ROC, Uncoated,
Convex Laser Mirror

[#27-623](#)

C\$194.40
[Volume Pricing](#)

1 In Stock

25.4mm Dia. x 75mm
ROC, Uncoated,
Convex Laser Mirror

[#27-626](#)

C\$194.40
[Volume Pricing](#)

2 In Stock

25.4mm Dia. x 100mm ROC, Uncoated, Convex Laser Mirror	#27-627	C\$194.40 Volume Pricing	2 In Stock
25.4mm Dia. x 150mm ROC, Uncoated, Convex Laser Mirror	#27-631	C\$194.40 Volume Pricing	1 In Stock
25.4mm Dia. x 200mm ROC, Uncoated, Convex Laser Mirror	#27-632	C\$194.40 Volume Pricing	5 In Stock
25.4mm Dia. x 300mm ROC, Uncoated, Convex Laser Mirror	#27-634	C\$194.40 Volume Pricing	2 In Stock
25.4mm Dia. x 400mm ROC, Uncoated, Convex Laser Mirror	#27-635	C\$194.40 Volume Pricing	2 In Stock
25.4mm Dia. x 500mm ROC, Uncoated, Convex Laser Mirror	#27-636	C\$194.40 Volume Pricing	2 In Stock
25.4mm Dia. x 1000mm ROC, Uncoated, Convex Laser Mirror	#27-637	C\$194.40 Volume Pricing	1 In Stock
25.4mm Dia. x 1500mm ROC, Uncoated, Convex Laser Mirror	#27-638	C\$194.40 Volume Pricing	1 In Stock
25.4mm Dia. x 2000mm ROC, Uncoated, Convex Laser Mirror	#27-639	C\$194.40 Volume Pricing	1 In Stock
25.4mm Dia. x 3000mm ROC, Uncoated, Convex Laser Mirror	#27-645	C\$194.40 Volume Pricing	1 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com