

[All Products](#) / [Lights and Illumination](#) / [Spectroscopy Lighting](#)

Digital Fiber Coupled LEDs



- Wavelengths from 275 - 940nm, with Broadband and White LED Options
- High Output Powers up to 250mW
- Integrated Driver and Controller for Ease of Use

Common Specifications

General

Operating Lifetime (hours): ~10,000

Contents of Kit:

- 1 x Fiber-coupled LED Unit
- 1 x 12V DC Power Supply
- 1 x International AC Socket Clip
- 1 x USB to RS232 adapter cable

Note: Fiberoptic Patch Cords sold separately

Hardware & Interface Connectivity

Connector: SMA

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Connector	Stock Number	Price	Buy
275.00	3	SMA	#70-896	C\$2,093.00 Volume Pricing	1 In Stock
280.00	3	SMA	#70-897	C\$2,093.00 Volume Pricing	1 In Stock
365.00	290	SMA	#70-898	C\$1,799.00 Volume Pricing	3 In Stock
395.00	350	SMA	#70-899	C\$1,799.00 Volume Pricing	1 In Stock
405.00	360	SMA	#70-900	C\$1,799.00 Volume Pricing	1 In Stock
455.00	320	SMA	#70-901	C\$1,799.00 Volume Pricing	1 In Stock
475.00	210	SMA	#70-902	C\$1,799.00 Volume Pricing	1 In Stock
490.00	140	SMA	#70-903	C\$1,953.00 Volume Pricing	1 In Stock
530.00	100	SMA	#70-904	C\$1,799.00 Volume Pricing	Contact Us
550.00	200	SMA	#70-905	C\$1,799.00 Volume Pricing	3 In Stock
595.00	100	SMA	#70-906	C\$1,799.00 Volume Pricing	1 In Stock
630.00	130	SMA	#70-907	C\$1,799.00 Volume Pricing	3 In Stock
680.00	130	SMA	#70-908	C\$1,953.00 Volume Pricing	1 In Stock
750.00	90	SMA	#70-909	C\$1,953.00 Volume Pricing	1 In Stock
810.00	140	SMA	#70-910	C\$1,953.00 Volume Pricing	1 In Stock
850.00	130	SMA	#70-911	C\$1,953.00 Volume Pricing	1 In Stock
940.00	120	SMA	#70-912	C\$1,953.00 Volume Pricing	1 In Stock

-	20	SMA	#70-913	C\$2,093.00 Volume Pricing	1 In Stock
-	220	SMA	#70-914	C\$1,953.00 Volume Pricing	1 In Stock
-	140	SMA	#70-915	C\$1,953.00 Volume Pricing	1 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com