



NOTES:

1. ALLOWABLE OPTICAL MATERIAL:
OPTICAL GRADE GERMANIUM
UNCOATED TRANSMISSION >45% AT 4 MICRONS
FOR 5mm THICK SAMPLE
2. CENTERING TOLERANCE:
BEAM DEVIATION: <3 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: NONE

 FINE GROUND SURFACE



FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING

	S1	S2	EFL (AT 10.6 microns)	35.00	 Edmund Optics®	
SHAPE	CONVEX	PLANO				
RADIUS	105.14	INFINITY	BFL (AT 10.6 microns)	34.25	TITLE	Ge Plano-Convex Lens, 25mm Dia. x 35mm FL, Uncoated
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	Ø 24	Ø 24				
BEVEL MAX FACE	0.3mm x 45°	0.3mm x 45°	ALL DIMS IN	mm	DWG NO	69639
						SHEET 1 OF 1