



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: IMA
 IMA: 0.000 MM
SPOT DIAGRAM

49794INK
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD :
 RMS RADIUS : 11.859
 GEO RADIUS : 34.873
 SCALE BAR : 100



REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49794INK
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 476.2402 μm
 DIFFRACTION LIMITED RANGE: 21.167 μm
 PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT

49794INK
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 200.000 \mu\text{m}$.
 0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49794INK
 TUE DEC 16 2008
 DATA FOR 0.4000 TO 1.0000 μm .
 SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)