



FOCAL LENGTH (EFL):  $9 \pm 0,09$   
 BACK FOCAL LENGTH (BFL): 8,46

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	9,02±0,009 CX	GLASS N-BK7 517/642	R	9,02±0,009 CX
Øe	2,5		Øe	2,5
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	5,8'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm
--------------------	----------------	-------------

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION

ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE: 3mm Dia, x 9mm FL Uncoated, Double-Convex Lens

DWG NO: 45131

SHEET SIZE: A4

SHEET 1 OF 1