



Features:

1. Wavelength range: 350-1100nm
2. Fixed gain low noise amplifier
3. Built-in 50 Ω load impedance
4. Equipped with $\pm 12V$ stabilized voltage supply

SPECIFICATIONS

Model	DA350-SI
Wavelength Range	350-1100nm
Sensitive Area	13mm ² (3.6*3.6mm)
Material	Si
Rise Time	10ns
Bandwidth	DC -12MHz
NEP	$1.2 \times 10^{-14} \text{W/Hz}^{1/2}$
Gain	50 Ω load (6.27KV/A)
Operating Temperature	10-50°C

