



FOCAL LENGTH (EFL): $150 \pm 1,5$
 BACK FOCAL LENGTH (BFL): $147,82$

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$68,789 \pm 0,069$ CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	24		Øe	24
3/	2 (0,2) $\lambda=632,8$ nm		3/	2 (0,2) $\lambda=632,8$ nm
4/	-		4/	2,18'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 25mm Diameter x 150mm FL, Uncoated, Laser Grade PCX Lens

DWG NO 67098

SHEET SIZE A4 SHEET 1 OF 1