

[All Products](#) / [Testing and Detection](#) / [Scratch Dig and Roughness Standards](#)

## NIST Traceable Scratch Dig Standards



- Feature Requirements in Accordance with ISO 10110-7 & ISO 14997
- First Surface Pattern for System Calibration or Coating Inspection
- Second Surface Pattern for Measuring Surface Defects

# Common Specifications

## General

Note:	Standards are for comparing optics against ISO 10110 specifications.
-------	--


### Physical & Mechanical Properties

Scale Divisions:	Every 0.025		
Scale Length (mm):	60 ±0.002	Width (mm):	50.80
Thickness (mm):	1.50	Dot Diameter Tolerance (mm):	±0.002
Line Width Tolerance (mm):	±0.002	Construction:	Black Anodized Aluminum Housing
Housing Tolerance (mm):	±0.2	Length (mm):	114.30

### Optical Properties

Substrate:	Float Glass	Surface Flatness (P-V):	3-4λ/inch
Surface Quality:	20-10 (inside active area)	Angle of Incidence (°):	45.00

Technical Information



## Products

Dot Diameter Tolerance (mm)	Line Width Tolerance (mm)	Surface Quality	Stock Number	Price	Buy
±0.002	±0.002	20-10	<a href="#">#59-154</a>	C\$1,414.00	8 In Stock
±0.002	±0.002	20-10	<a href="#">#59-156</a>	C\$1,414.00	6 In Stock
±0.002	±0.002	20-10	<a href="#">#59-155</a>	C\$1,414.00	Contact Us



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)