

FOCAL LENGTH (EFL): $-50 \pm 0,5$
 BACK FOCAL LENGTH (BFL): $-52,31$

1 AR COATING: YAG-BBAR
 R(abs) $< 0.25\%$ @ 532nm
 R(abs) $< 0.25\%$ @ 1064nm
 R(avg) $< 1.0\%$ @ 500 - 1100nm

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$25,84 \pm 0,026$ CV	GLASS N-BK7 517/642	R	∞ PL
Øe	24		Øe	24
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



Edmund Optics®

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm

TITLE

LENS PCV 25 X -50 YAGBBAR TS

DWG NO

21320

SHEET SIZE
A4

SHEET
1 OF 1