




NOTES:
1. SUBSTRATE:
N-BK7

2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: NONE
S2: Ravg >98% @ 400 - 750nm (0 - 45°)
Ravg >99% @ 400 - 750nm (0 °)

3. FINE GRIND SURFACE

4. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

	S1	S2
SHAPE	PLANO	PLANO
ANGLE TOL. (arcmin)	±2	±2
POWER (FRINGES) @ 632.8nm	1.25	1.25
IRREGULARITY (FRINGES) @ 632.8nm	0.50	0.50
CLEAR APERTURE	95.46 x 67.50	67.50 x 67.50
COATING APERTURE	N/A	67.50 x 67.50
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 	TITLE	75mm, 400 - 750nm Broadband Dielectric,N-BK7 90° Specialty Mirror		
	DWG NO	26457	SHEET 7 OF 7	