




NOTES:


1. SUBSTRATE: Polymer Film XP40HT-40
2. WAVELENGTH RANGE: 400 - 700 nm
3. POLARIZATION EFFICIENCY (%): >99.5
4. TRANSMISSION (%):  
 SINGLE: 40 ±2  
 PARALLEL: 32.2  
 CROSSED: <0.005
5. EXTINCTION RATIO: 5000:1
6. TEMPERATURE RESISTANCE (°C x HOURS):  
 HEAT: 100 x 1,000  
 COLD: -40 x 1,000  
 HUMIDITY: 80 x 90% RH x 1,000
7. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	50mm Dia. High-Temperature Linear Polarizing Film (XP40HT-40)	
ALL DIMS IN	mm	DWG NO	29478	SHEET 6 OF 12