


NOTES:

1. SUBSTRATE:
FUSED SILICA
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE
3. FINE GRIND SURFACE
4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div><div><div>THIRD ANGLE PROJECTION</div></div><div>ALL DIMS IN mm</div><div><div>TITLE</div><div>DWG NO</div></div><div><div>25.4mm Dia. x 1500mm ROC, Uncoated, Concave Laser Mirror</div><div>27579</div></div><div><div>SHEET 6 OF 21</div></div></div>
SHAPE	CONCAVE	PLANO	
RADIUS	1500	INFINITY	
SURFACE QUALITY	20-10	N/A	
CLEAR APERTURE	Ø 22.86	N/A	
IRREGULARITY AT 632.8nm	λ/10	N/A	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	

EO® **Edmund Optics®**