

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Double-Convex \(DCX\) Lenses](#)

ISP Optics Calcium Fluoride Double-Convex (DCX) Lenses

See

More by [ISP Optics](#)



- Greater than 90% Transmission from 350nm-7µm
- Low Index of Refraction
- High Laser Damage Threshold

Common Specifications


Physical & Mechanical Properties

Centering (arcmin):	<3	Bevel:	Protective as needed
---------------------	----	--------	----------------------


Optical Properties

Coating:	Uncoated	Substrate:	Calcium Fluoride (CaF₂)
Surface Quality:	60-40	Irregularity (P-V) @ 632.8nm:	λ
Focal Length Tolerance (%):	±2	Wavelength Range (nm):	300 - 8000


Technical Information





Calcium Fluoride



Uncoated



Products

Dia. (mm)	EFL (mm)	Coating	Substrate	Model Number	Stock Number	Price	Buy
#24-763 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
12.70	25.40	Uncoated	Calcium Fluoride (CaF₂)	CF-BX-12-25		C\$198.86 Volume Pricing	8 In Stock
#24-765 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
25.40	150.00	Uncoated	Calcium Fluoride (CaF₂)	CF-BX-25-150		C\$406.62 Volume Pricing	5 In Stock

[#24-767 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

38.10	50.80	Uncoated	Calcium Fluoride (CaF₂)	CF-BX-38-50	C\$609.92 Volume Pricing	3 In Stock
-------	-------	----------	--	-------------	---	------------

[#24-768 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

38.10	63.50	Uncoated	Calcium Fluoride (CaF₂)	CF-BX-38-63	C\$609.92 Volume Pricing	7 In Stock
-------	-------	----------	--	-------------	---	------------

