

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [UV and IR Windows](#)

## Pure (Undoped) YAG Windows




- Excellent Mid-Wave IR (MWIR) (4 - 5 $\mu$ m) Transmission
- Available in 5, 10, 12.5, and 25mm Diameters
- Commonly Used in White Light Generation



Common Specifications

Physical & Mechanical Properties			
Bevel:	Protective as needed	Clear Aperture (%):	90
Thickness (mm):	1.00 ±0.1	Edges:	Fine Ground
Knoop Hardness (kg/mm²):	1,215.00	Parallelism (arcmin):	<3
Poisson's Ratio:	0.28	Young's Modulus (GPa):	300
Optical Properties			
Abbe Number (v <sub>d</sub> ):	56	Axis Orientation:	<100>
Coating:	Uncoated	Index of Refraction (n <sub>d</sub> ):	1.81
Substrate:	Yttrium Aluminium Garnet (YAG)	Surface Quality:	40-20
Wavelength Range (nm):	210 - 5500		
Material Properties			
Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):		8.2	
Density (g/cm³):		4.56	

## Technical Information



## Products

Dia. (mm)	Thickness (mm)	Stock Number	Price	Buy
5.00	1.00	<a href="#">#19-541</a>	C\$270.09 <a href="#">Volume Pricing</a>	20+ In Stock
10.00	1.00	<a href="#">#19-542</a>	C\$308.67 <a href="#">Volume Pricing</a>	20+ In Stock
12.50	1.00	<a href="#">#19-543</a>	C\$385.84 <a href="#">Volume Pricing</a>	20+ In Stock
25.00	1.00	<a href="#">#19-545</a>	C\$501.59 <a href="#">Volume Pricing</a>	20+ In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)