

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Ultrafast Laser Mirrors](#)

TECHSPEC®

PeakPower High LDT Low GDD Ultrafast Mirrors



- High Femtosecond Laser Damage Threshold exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm
- > 99.5% Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

Common Specifications

Physical & Mechanical Properties

Edges:	Commercial Polish	Bevel:	Protective as needed
Optical Properties			
Surface Quality:	10-5	Surface Flatness (P-V):	λ/10

Technical Information

Products

Title	Stock Number	Price	Buy
PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 12.7mm Dia., 6.35mm Thick	#29-520	C\$415.52 Volume Pricing	11 In Stock
PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 25.4mm Dia., 6.35mm Thick	#29-521	C\$608.44 Volume Pricing	20+ In Stock
PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 50.8mm Dia., 9.53mm Thick	#29-522	C\$1,061.06 Volume Pricing	4 In Stock
Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 12.7mm Dia., 6.35mm Thick	#29-523	C\$489.72 Volume Pricing	20+ In Stock
Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 25.4mm Dia., 6.35mm Thick	#29-524	C\$682.64 Volume Pricing	20+ In Stock
Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 50.8mm Dia., 9.53mm Thick	#29-525	C\$1,135.26 Volume Pricing	10 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com