

TECHSPEC[®] 20mm, Al & AR Coated, Fused Silica, Right Angle Prism



TECHSPEC UV Fused Silica Right Angle Prisms

Stock **#47-795** **16 In Stock**

-

1

+

C\$192⁰²

ADD TO CART

Volume Pricing	
Qty 1-5	C\$192.92 each
Qty 6-25	C\$160.27 each
Qty 26-49	C\$154.34 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:
Right Angle Prism

Physical & Mechanical Properties

Dimensional Tolerance (mm):	
±0.10 Legs	
Bevel:	
Protective as needed	
Length of Hypotenuse (mm):	
28.30	
Length of Legs (mm):	
20.00	
Optical Properties	
Coating:	
MgF ₂ & Aluminized	
Substrate: ☐	
Fused Silica (Corning 7980)	
Surface Quality:	
60-40	
Angle Tolerance (arcmin):	
±5	
Pyramid Tolerance (arcmin):	
±5	
Image Orientation:	
Left-Handed	
Coating Specification:	
Hypotenuse: R _{avg} >85% @ 400 - 700nm Legs: R _{avg} ≤1.75% @ 400 - 700 nm	
Ray Deviation (°):	
90	
Wavelength Range (nm):	
400 - 700	
Damage Threshold, By Design: ☐	
Hypotenuse: 0.3 J/cm ² @ 532nm & 1064nm, 10ns Legs: 10 J/cm ² @ 532nm, 10ns	
Power (fringes) @ 632.8nm:	
1.25	
Irregularity (fringes) @ 632.8nm:	
0.25	


Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 235:	
Compliant	

PRODUCT DETAILS

- Ideal for Broadband Applications
- Available with Aluminized and AR Coated Faces
- Sizes Ranging from 5 - 50mm
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® UV Fused Silica Right Angle Prisms are ideal for broadband applications. Right angle prisms are generally used to bend image paths or redirect light at 90°. This produces a left-handed image and depending on the orientation of the prism, the image may be inverted or reverted. Right angle prisms can also be used in combination for image/beam displacement. TECHSPEC® UV Fused Silica Right Angle Prisms are made from UV fused silica which features low thermal expansion and excellent transmission throughout the UV, visible, and NIR spectral ranges. The prisms are available in lengths ranging from 5 to 50mm.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
