


ZAP-IT® Laser Alignment Paper, 4 x 8", Box of 50 Sheets



Stock **#90-709** 20+ In Stock

-

1

+

C\$274^{.89}

ADD TO CART

Volume Pricing	
Qty 1+	C\$274.89 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Note:

Recommended Pulsed Width: 1ns to 30ms
Recommended Power Level Range: 5 mJ/cm² to 20 J/cm²

Physical & Mechanical Properties

Thickness (inches):

0.009	
	Thickness (mm):
0.24	
	Sheet Size (in):
4 x 8	
	Sheet Size (mm):
101.6 x 203.2	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 247:
Compliant	

PRODUCT DETAILS

- Industrial Standard Beam Profile Viewing Paper
 - Records Beam Shape, Divergence, Mode, and Intensity Profile of Pulsed Lasers
 - Suitable for Broadband Sources from UV to IR
- ZAP-IT® Laser Alignment Paper is designed to test the characteristics of pulsed laser sources from the ultraviolet to infrared. Beam characteristics are recorded by holding the ZAP-IT® Laser Alignment Paper in the beam path. ZAP-IT® Laser Alignment Paper is ideal for use in alignment applications or with [laser optics](#) including laser beam expanders, optical lenses, apertures, attenuators, or power meters. For continuous wave lasers, use a mechanical chopper, Q-switch, or manually switch the laser on and off rapidly to create short pulses.
- Note:** It may be difficult to see the beam characteristics when the input beam diameter is 1/4"/6.35mm or less. If so, use a [beam expander](#) or [plano convex lens](#) to magnify the beam diameter. If using a plano convex lens, place ZAP-IT® Laser Alignment Paper at an image distance of 2.5 times longer than the focal length of the lens.