


NOTES:

- 1. SUBSTRATE:
ZERODUR®
- 2. S2 TO BE PARALLEL TO S1 TO WITHIN <30 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1&S2:
Ravg >98% @ 400 - 750nm (0 - 45°) Ravg >99% @ 400 - 750nm (0°)

4. FINE GRIND SURFACE



5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	COMMERCIAL POLISH
CLEAR APERTURE	Ø 13.5	N/A
SURFACE FLATNESS	λ/10	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	15mm Dia. 400 - 750nm Broadband λ/10 ZERODUR® Mirror
ALL DIMS IN	mm	DWG NO	24023
			SHEET 8 OF 18