




NOTES:
1. SUBSTRATE:
N-BK7

2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: NONE
S2: Ravg >98% @ 400 - 750nm (0 - 45°)
Ravg >99% @ 400 - 750nm (0 °)

3. FINE GRIND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
ANGLE TOL. (arcmin)	±2	±2
POWER (FRINGES) @ 632.8nm	1.25	1.25
IRREGULARITY (FRINGES) @ 632.8nm	0.50	0.50
CLEAR APERTURE	31.82 x 22.50	22.50 x 22.50
COATING APERTURE	N/A	22.50 x 22.50
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

TITLE	25mm, 400 - 750nm Broadband Dielectric,N-BK7 90° Specialty Mirror		
DWG NO	26455	SHEET 5 OF 7	