



- NOTES:
- 1. SUBSTRATE:
N-BK7
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NIR I (600-1050nm)
R(avg) ≤0.5% @ 600 - 1050nm
 - 3. FINE GROUND SURFACE
 - 4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
 - 5. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	25.00	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL	23.02			
RADIUS	12.92	∞			TITLE	10mm H x 10mm L x 25mm FL NIR I Coated, Illumination Grade PCX Cylinder Lens	
SURFACE QUALITY	60 - 40	60 - 40					
CLEAR APERTURE	9.00 x 9.00	9.00 x 9.00	ALL DIMS IN	mm	DWG NO	25485	SHEET 2 OF 16
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					